

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1552400020

Status:

Active

Overview:

Flamar Standard and Custom Cables for Industrial Automation

Description:

Flamar Sensor Cable, TPE Jacket, Unshielded, 4 Circuits, 0.34mm² / 22 AWG, 5.40mm (.213") Diameter, 800.0m (2624.67') Length, Yellow

Documents:

Product Specification 1552400001-P1E (PDF)

RoHS Certificate of Compliance (PDF)

Brochure (PDF)

Agency Certification

CSA

LL107556

UL

E470965

General

Product Family

Cable

Series

155240

Crimp Quality Equipment

Yes

Geographic Area

Global

Overview

Flamar Standard and Custom Cables for Industrial Automation

Product Name

Flamar, Signal and Control

Taxonomy

Industrial Cable

UPC

889056452793

Physical

Bending Radius - Minimum

> 10xOD

Cable Length

800.0m

Circuits (Loaded)

4

Color - Cable Jacket

Yellow

Insulation

PVC

Material - Outer Jacket

TPE

Net Weight

0.040/kg

Outer Jacket Diameter

5.40mm

Packaging Type

Reel

Temperature Range - Operating

-40° to +105°C

Wire Size AWG

22

Wire Size mm²

0.34

Wire/Cable Type

UL Listed PLTC

Electrical

Current - Maximum per Contact

Contact Molex

Voltage - Maximum

300V

Material Info


Engineering Number

1X800M

Reference - Drawing Numbers

Product Specification

1552400001-P1E



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained per -
D(2022)4187-DC (10
June 2022)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

155240 Series

Use With

Nano-Change (M8) [120091](#) , Micro-Change (M12) [120071](#) , Ultra-Lock (M12) [120085](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION