




REVISIONS			
REV	DESCRIPTION, ECN, EAR NO.	DATE	APP'D
A	PROPOSAL	SEP 03/18	L.CHAN
B	PROPOSAL	OCT 30/19	L.CHAN




MATERIALS:
RJ:
HOUSING & COVER: ENGINEERING THERMOPLASTIC
FLAMMABILITY RATING UL 94V-0, COLOUR: BLACK
CONTACTS: PHOSPHOR BRONZE
PLATING: SELECTIVE GOLD PLATING ON MATING SURFACES
SEE AMPHENOL PART NUMBER FOR DETAIL.
50 μ” [1.27 MICRONS]
MIN. NICKEL UNDERPLATE
100 μ” TIN PLATING ON CONTACT TAILS.
SHIELD: STAINLESS STEEL, WITH TIN-DIP ON SOLDER TABS.

USB:
HOUSING: ENGINEERING THERMOPLASTIC
FLAMMABILITY RATING UL 94V-0,
COLOUR: BLUE
CONTACTS: PHOSPHOR BRONZE
PLATING: SELECTIVE GOLD FLASH ON MATING SURFACES
50 μ” [1.27 MICRONS]
MIN. NICKEL UNDERPLATE
100μ” TIN PLATING ON CONTACT TAILS
SHIELD: STAINLESS STEEL WITH NICKEL.

AMPHENOL PART NUMBER: RJE36-188-3X05

GOLD PLATING
0 = GOLD FLASH
1 = 6 μ INCH
2 = 15 μ INCH
3 = 30 μ INCH
4 = 50 μ INCH



UNLESS SPECIFIED OTHERWISE	DRAWN HANSON.C	DATE SEP 03/18	Amphenol Canada Corp. Commercial Products	
PRIMARY UNITS MILLIMETER	CHECKED AMY.Z	SEP 03/18		
SECONDARY	M.E. APP'D		TITLE RJ45 OVER TWO USB 3.0 COMBO, DIP TYPE WITH TABS, WITHOUT LEDS-RoHS COMPLIANT	
REFERENCE IN PARENTHESES	Q.A. APP'D			
GENERAL TOLERANCES	DWG APPR. L.CHAN	SEP 03/18	DWG. NO. P-RJE36-188-3X05	
1 DECIMAL PLACE ±0.30	ENG. REL. NO.			
2 DECIMAL PLACES ±0.25	REF.		CODE ID NO. 03554 DWG SIZE: C SCALE: N/A SHEET 1 OF 1	
3 DECIMAL PLACES ±0.20	THIRD ANGLE PROJECTION	DO NOT SCALE DRAWING		
ANGULAR DEGREES ±1.0°			REV B	

THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION AND SUCH INFORMATION MAY NOT BE DISCLOSED TO OTHERS FOR ANY PURPOSE OR USED FOR MANUFACTURING PURPOSES WITHOUT WRITTEN PERMISSION FROM AMPHENOL CANADA CORP.