







PART NUMBER SEE SHEET 2



spec ref		*		dr		Rainbow Zhan	2014/08/12		projection				size		A3		scale		3:2				
tolerance std		TOLERANCES UNLESS OTHERWISE SPECIFIED		eng		Rainbow Zhan		2014/08/21						ecn no		-							
chr				LI-He		2014/08/20		rel level						Released									
ASME Y14.5				appr		Pei-Ming Zheng		2014/08/21						product family		PwrBlade+							
surface				linear		0.X		±0.5				title		4HP+20S+3HDP+20S+4HDP		dwg no		10106267-B010001		rev		A	
				0.XX		±0.25																	
				0.XXX		±0.10																	
ASME Y14.5		angular		0°		±2°		www.fci.com		cat. no.		Product - Customer Drw		sheet 1 of 3									

A

B

C

D


A

B

C

D

- NOTES:
- 1) "FCI", PART NUMBER AND DATE CODE TO BE MARKED ON THIS SURFACE.
THE MARK CAN BE OMITTED IF THERE IS NOT ENOUGH SPACE ON THIS SURFACE.
- 2) MATERIALS:
-HOUSING - GLASS FILLED WITH HIGH TEMP THERMOPLASTIC, UL94V-0.
-SIGNAL CONTACT - COPPER ALLOY.
-POWER CONTACT - HIGH CONDUCTIVITY COPPER ALLOY.
- 3) PLATING SPECIFICATION REFER TO FCI 10116351
- 4) DENOTES CONNECTOR KEEP OUT ZONE.
- 5) DATUM AND BASIC DIMENIONS WERE ESTABLISHED BY CUSTOMER.
- 6) ALL HOLE DIAMETERS ARE FINISHED HOLE SIZES.
- 7) 1.15±0.025MM DRILLED HOLE PLATED WITH 0.00762MM MIN Sn
OVER 0.0254-0.0762MM Cu PLATING TO ACHIEVE A 1.02±0.07MM HOLE.
- 8) PRODUCT SPECIFICATION REFER TO FCI GS-12-658.
APPLICATION SPECIFICATION REFER TO FCI GS-20-141.
PRODUCT PACKAGED IN TRAYS, REFER TO FCI GS-14-1502.



dr	Rainbow Zhan	2014/08/12	<div>projection</div> <div></div>	<div>MM</div> <div></div>	size	A3	scale	3:2
eng	Rainbow Zhan	2014/08/21			ecn no	-		
chr	Li-He	2014/08/20			rel level	Released		
appr	Pei-Ming Zheng	2014/08/21	product family		PwrBlade+			
<div>www.fci.com</div>		cat. no.			Product - Customer Drw			sheet 3 of 3
<div>FCi</div>		title			dwg no		rev	
		4HP+20S+3HDP+20S+4HDP VERTICAL PF HEADER			10106267-B010001		A	