



Part Number : [638118200](#)
Product Description : PremiumGrade Hand Crimp Tool for KK 2.54mm Crimp Terminals, 30-22 AWG
Series Number : 207129
Status : Active
Product Category : Crimp Presses and Crimp Hand Tools



Documents & Resources

Tooling Specifications

- [ATS-638118200-001.pdf](#)
- [TM-638000029-001.pdf](#)
- [TM-638000029DE-001.pdf](#)
- [TM-638000029SP-001.pdf](#)
- [TM-638000029FR-001.pdf](#)
- [TM-638000029IT-001.pdf](#)
- [TM-638000029JP-001.pdf](#)
- [TM-638000029KR-001.pdf](#)
- [TM-638000029MY-001.pdf](#)
- [TM-638000029PL-001.pdf](#)
- [TM-638000029RU-001.pdf](#)
- [TM-638000029SK-001.pdf](#)
- [TM-638000029TH-001.pdf](#)
- [TM-638000029VN-001.pdf](#)
- [TM-638000029CN-001.pdf](#)
- [TM-638000029TW-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Relevant
REACH SVHC	Not Contained per D(2022)4187-DC (10 June 2022)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Crimp Presses and Crimp Hand Tools
Series	207129
Description	PremiumGrade Hand Crimp Tool for KK 2.54mm Crimp Terminals, 30-22 AWG
Comments	See Tooling Specification (PDF) Above; Type: 4D
Function	Crimp
Geographic Area	Global
Level of Automation	Manual
More Detailed Tech Information	toolingsupport@molex.com
Product Family	Application Tooling
Product Name	PremiumGrade
Tool Type	Hand Crimp Tool
UPC	800756956992

Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.
---------------------	--

Physical

Net Weight	332.600/g
------------	-----------

Applicable Parts

Description	Part Number
KK 254 Cat Ear Crimp Terminal 4809, 30-22 AWG, Hot Tin Dip, Bag	<u>08500032</u>
KK 254 Crimp Terminal, 30-22 AWG, Bag, Tin (Sn) Plating, Nickel (Ni) Under Plating	<u>08500160</u>
KK 254 Crimp Terminal 6459, 30-22 AWG, Bag, Phosphor Bronze Tin (Sn)	<u>08520123</u>
KK 254 Crimp Terminal, 30-22 AWG, Bag, Selective Gold (Au), Nickel (Ni) Under Plating	<u>08550102</u>
KK 254 Crimp Terminal, 30-22 AWG, Bag, Selective Gold (Au), Nickel (Ni) Under Plating	<u>08550131</u>
KK 254 Crimp Terminal, 30-22 AWG, Bag, Gold (Au), Nickel (Ni) Under Plating	<u>08560110</u>
KK 254 Cat Ear Crimp Terminal 41572, Bag Tin (Sn)	<u>08650805</u>
KK 254 Crimp Terminal 6459, 30-22 AWG, Bag, Phosphor Bronze Gold (Au)	<u>08650814</u>
KK 254 Crimp Terminal 6459, 30-22 AWG, Bag, Phosphor Bronze Selective Gold (Au)	<u>08650816</u>

KK Cat Ear Crimp Terminal 5159, 28-22 AWG, Bag, Phosphor Bronze, Tin (Sn) Plating	<u>08700049</u>
KK Cat Ear Crimp Terminal 5159, 28-22 AWG, Bag, Brass, Tin (Sn) over Copper Plating	<u>08700069</u>
KK 254 Crimp Terminal, 28-22 AWG, 0.35µm Gold (Au), Nickel (Ni) Under-Plate, Brass, Loose	<u>39000377</u>
KK 254 Crimp Terminal, 28-22 AWG, 0.35µm Gold (Au), Nickel (Ni) Under-Plate, Phosphor Bronze, Loose	<u>39000381</u>

This document was generated on Oct 08, 2024