



Tous droits strictement réservés. Reproduction ou communication à des tiers interdite sous quelque forme que ce soit sans autorisation écrite du propriétaire. Propriété de c FCI. Droits de reproduction FCI.



All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.

PRODUCT NO.	ROWS	SIG.				POWER							E1
		E2	3	2	1	P7	P6	P5	P4	P3	P2	P1	
51923-001-- NOTE: ③	D C B A		H G F E	H G F E	H G F E	X	PA	PA	PA	PG	X	PG	
													



CODE	DIM "M" MATING LENGTH	CONTACT TYPE
E	N/A [N/A]	SIGNAL
F	N/A [N/A]	SIGNAL
G	N/A [N/A]	SIGNAL
H	N/A [N/A]	SIGNAL
PA	.042 [1.07]	POWER
PG	.042 [1.07]	POWER
HA	N/A [N/A]	HOLD-DOWN
X	OMITTED	OMITTED

mat'l code				SEE NOTE 2		tolerances unless otherwise specified		CUSTOMER		FCI		www.fciconnect.com	
ltr	ecn no.	dr	date					COPY		projection		title	
A	V03-0129	TAB	01/29/03	linear		.XX±.01/0.X±0.3						3ACP + 4P + 12S	
B	DG05-0192	SJ	06/27/05			.XXX±.005/0.XX±0.13						R/A SOLDER RECEPTACLE	
C	DG08-0273	WD	12/10/08	angles		.XXX±.0020/0.XXX±0.051							
						0°±2°							
				dr	T. BRUNGARD	01/29/03				INCH/MM		product family	PwrBlade
				enrg	M. MOSTOLLER	01/29/03				scale		size	dwg no
				chr	M. MOSTOLLER	01/29/03				1:1		A	51923-001
				appd	M. MOSTOLLER	01/29/03						code	213
sheet index	revision	sheet	C	C	C	C						sheet	1 of 4
			1	2	3	4							

Pro/E


cage code 22526

Tous droits strictement réservés. Reproduction ou communication à des tiers interdite sous quelque forme que ce soit sans autorisation écrite du propriétaire. Propriété de c FCI. Droits de reproduction FCI.




All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.


PRODUCT NUMBER
51923-001--
NOTE: ③




BROKEN-OUT SECTION A-A
SCALE 2:1





BROKEN-OUT SECTION B-B
SCALE 2:1



SECTION C-C



SECTION F-F
SCALE 2:1

mat'l code SEE NOTE 2				tolerances unless otherwise specified		CUSTOMER		 www.fciconnect.com		
litr	ecn no.	dr	date	linear	.XX±.01/0.X±0.3	COPY		title 3ACP + 4P + 12S R/A SOLDER RECEPTACLE	product family PwrBlade	code 213
C					.XXX±.005/0.XX±0.13		projection			
					.XXX±.0020/0.XXX±0.051					
				angles	0°±2°		scale	size A	dwg no 51923-001	sheet 2 of
				dr	T. BRUNGARD 01/29/03					
				enrg	M. MOSTOLLER 01/29/03					
				chr	M. MOSTOLLER 01/29/03	1:1	scale	A	size	dwg no
				appd	M. MOSTOLLER 01/29/03					
sheet index	revision	sheet								


Pro/E

cage code 22526



All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.

Tous droits strictement réservés. Reproduction ou communication à des tiers interdite sous quelque forme que ce soit sans autorisation écrite du propriétaire. Propriété de c FCI. Droits de reproduction FCI.



Pro/E

PDM: Rev:C

STATUS: Released

Printed: Dec 20, 2010

Tous droits strictement reserves. Reproduction ou communication a des tiers interdite sous quelque forme que ce soit sans autorisation écrite du propriétaire.
Propriete de c FCI. Droits de reproduction FCI.



All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor.
Property of FCI. Copyright FCI.

PRODUCT NUMBER
51923-001--
NOTE: ③

NOTES:

1. DIMENSIONS AND TOLERANCES ARE IN ACCORDANCE WITH ASME Y14.5M, 1994 UNLESS OTHERWISE SPECIFIED.

CONNECTOR NOTES:

- ② HOUSING MATERIAL: UL 94 V-0 GLASS FILLED HIGH-TEMP THERMOPLASTIC
POWER CONTACT MATERIAL: COPPER ALLOY
SIGNAL PIN MATERIAL: COPPER ALLOY

△ 3. SEE ITEM 5 & 6 IN PRINT 10064183 FOR PLATING SPEC OF 51923-001 AND 51923-001LF RESPECTIVELY.

- ④ MANUFACTURER'S NAME, P/N, AND DATE CODE TO APPEAR ON THIS SURFACE.

5. PRODUCT SPECIFICATION GS-12-149.
APPLICATION SPECIFICATION BUS-20-067.

6. PACKAGED IN TRAYS.

PCB NOTES:

7. ALL HOLE DIAMETERS ARE FINISHED HOLE SIZE.

- ⑧ MOUNTING HOLES, WHERE APPLICABLE, ARE UNPLATED.

- ⑨ $\varnothing .0453 \pm .0010$ [1.151 $\pm$ 0.025] DRILLED HOLES PLATED WITH
.0003 [0.008] MIN SnPb OVER .001 [0.03]
TO .003 [0.08] Cu PLATING TO ACHIEVE
 $\varnothing .040 \pm .003$ [1.02 $\pm$.07] HOLE.

- ⑩ "DIM XXX" TO BE DETERMINED BY THE CUSTOMER.

- ⑪ CONNECTOR KEEP-OUT ZONE.

12. △ SYMBOL WILL BE NEXT TO ANY DIMENSION, VIEW, OR NOTE WHICH HAS BEEN MODIFIED
WITH THE CURRENT DRAWING REVISION.

mat'l code				SEE NOTE 2				tolerances unless otherwise specified				CUSTOMER								www.fciconnect.com							
ltr		ecn no.		dr		date		linear		.XX+.01/0.X+.0.3		COPY								title 3ACP + 4P + 12S R/A SOLDER RECEPTACLE							
C										.XXX+.005/0.XX+.0.13		projection															
								angles		.XXX+.0020/0.XXX+.0.051						product family PwrBlade				code 213							
										0° ± 2°														INCH/MM			
								dr		T. BRUNGARD 01/29/03		scale 1:1				size A				dwg no 51923-001				sheet 4 of 4			
								engr		M. MOSTOLLER 01/29/03																	
								chr		M. MOSTOLLER 01/29/03																	
								appd		M. MOSTOLLER 01/29/03																	
sheet index		revision sheet																									

cage code 22526