Part Number : 2012010150
Product Description : Spot-On Wire-to-Board Header with Nail, 2.00mm Pitch, Single Row, Vertical, 15 Circuits, with Potting Capability, Matte Tin (Sn) Plating, Natural
Series Number : 201201
Status : Active
Product Category : PCB Headers and Receptacles



Documents and Resources

Drawings

2012010150_sd.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Symbol and Footprint (Multi-Format)

Specifications

2011960000-A00.pdf

2011960000-A01.pdf

2012019200-200.pdf

2012000000-PS-000.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)

Downloaded from Arrow.com.

EU RoHS	Compliant per EU 2015/863

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	PCB Headers and Receptacles
Series	201201
Description	Spot-On Wire-to-Board Header with Nail, 2.00mm Pitch, Single Row, Vertical, 15 Circuits, with Potting Capability, Matte Tin (Sn) Plating, Natural
Application	Wire-to-Board
Component Type	PCB Header
Keyword	Spot-On 2.0
Product Name	Spot-On
UPC	191128253673

Electrical

Current - Maximum per Contact	3.0A
Voltage - Maximum	250V AC (RMS)/DC

Physical

Downloaded from Arrow.com.

Breakaway	No
Circuits (Loaded)	15
Circuits (maximum)	15
Color - Resin	Natural
Durability (mating cycles max)	30
First Mate / Last Break	No
Gender	Male
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Polyamide (PA)
Net Weight	3312.630/mg
Number of Rows	1
Orientation	Vertical
Packaging Type	Embossed Tape on Reel
PCB Locator	No
PCB Retention	Yes
Pitch - Mating Interface	2.00mm
Pitch - Termination Interface	2.00mm
Plating min - Mating	1.000µm
Plating min - Termination	1.000µm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Shrouded	Shrouded
Stackable	No
Temperature Range - Operating	-40° to +105°C
Termination Interface Style	Surface Mount

Mates With / Use With

Mates with Part(s)

Downloaded from Arrow.com.

Description	Part Number
2.00mm Pitch, Spot-On Single Row Receptacle Housings	201200

This document was generated on Jun 10, 2026

Downloaded from Arrow.com.