


10091830 - X X X X X L F

LEAD-FREE DESIGNATION ADDED
ONLY WHEN APPLICABLE




SCALE 3:1

PLATING CODE	
I	SEPARABLE INTERFACE: PERFORMANCE-BASED PLATING, TELCORDIA CO (SEE NOTE 2) PRESS-FIT TAILS: TIN OR TIN-LEAD BASED ON LEAD-FREE "LF" SUFFIX
5	SEPARABLE INTERFACE: PERFORMANCE-BASED PLATING, TELCORDIA UE (SEE NOTE 2) PRESS-FIT TAIL: TIN OR TIN-LEAD ON BASED ON LEAD-FREE "LF" SUFFIX
D	SEPARABLE INTERFACE: CUSTOMER SPECIFIC PLATING PRESS-FIT TAIL: TIN OR TIN-LEAD ON BASED ON LEAD-FREE "LF" SUFFIX
E	SEPARABLE INTERFACE: CUSTOMER SPECIFIC PLATING PRESS-FIT TAIL: TIN OR TIN-LEAD ON BASED ON LEAD-FREE "LF" SUFFIX

SEQUENTIALLY ASSIGNED FOR CUSTOM LOADING CONFIGURATIONS (SEE TABLE, SHEET 5)
"00" FOR STANDARD LOADING (UNIFORM CONTACT LENGTH, ALL POSITIONS)


CONTACT WIPE LENGTH	
0	CUSTOM LOADED CONTACTS
1	4.5mm ALL CONTACTS
2	6.0mm ALL CONTACTS
3	7.5mm ALL CONTACTS

NUMBER OF POWER SLOTS	
1	ONE POWER SLOT ("1-UP" MODULE)
2	TWO POWER SLOTS ("2-UP" MODULE)
3	THREE POWER SLOTS ("3-UP" MODULE)




1-SLOT POWER MODULE
MATING-FACE VIEW

SCALE 4:1




2-SLOT POWER MODULE
MATING-FACE VIEW

SCALE 4:1



3-SLOT POWER MODULE
MATING-FACE VIEW

SCALE 4:1




spec ref	SEE NOTES	dr	Jim Swain	2009/07/23	projection	mm	size	A2	scale	4:1
tolerance std	TOLERANCES UNLESS OTHERWISE SPECIFIED	eng	Lin-Soe Ngwe	2012/11/19	chr	-	ecn no	-	rel level	Released
ASME Y14.5		appr	Chen-Hong Tan	2012/11/19	product family		cat. no.	10091830	rev	A
surface	linear	0.X	±0.25	0.XX	±0.13	0.XXX	±-	angular	0°	±°
ASME Y14.5		www.fci.com								

PDS: Rev :A



STATUS:Released

Printed: Nov 20, 2012


TABLE 1. VARIABLE FOOTPRINT DIMENSIONS				
	DIM A	DIM B	DIM C	DIM D
1-SLOT POWER MODULE	7.40	4.81	12.21	6.66
2-SLOT POWER MODULE	14.80	12.21	19.61	14.06
3-SLOT POWER MODULE	22.20	19.61	27.01	21.46






POWER MODULE FOOTPRINT LOCATION RELATIVE TO XCede SIGNAL MODULES


spec ref		SEE NOTES			dr		Jim Swain		2009/07/23		projection				mm		size		A2		scale		4:1	
tolerance std		TOLERANCES UNLESS OTHERWISE SPECIFIED			eng		Lin-Soe Ngwe		2012/11/19						ecn no		-		rel level		Released			
ASME Y14.5					chr		-		-															
		appr		Chen-Hong Tan		2012/11/19		product family		XCede														
surface				linear		0.X		±0.25				title		MODULE ASSEMBLY, POWER		dwg no		10091830		rev		A		
				0.XX		±0.13																		
ASME Y14.5				0.XXX		±-																		
angular		0°		±-°		www.fci.com		cat. no.		SEE P/N TABLE		Product - Customer Drw		sheet 2 of 5										

SEE TABLE I.





POWER MODULE FOOTPRINT LOCATION RELATIVE TO XCede SIGNAL MODULES

spec ref	SEE NOTES			dr	Jim Swain	2009/07/23	projection		mm	size	A2	scale	1:1	
tolerance std	TOLERANCES UNLESS OTHERWISE SPECIFIED			eng	Lin-Soe Ngwe	2012/11/19			ecn no	-				
ASME Y14.5				chr	-	-			rel level	Released				
	appr	Chen-Hong Tan	2012/11/19	product family					-					
surface		linear	0.X	±0.25		title	MODULE ASSEMBLY, POWER XCede 4-PAIR BP VERTICAL, STANDARD PROFILE			dwg no	10091830		rev	A
ASME Y14.5			0.XX	±0.13										
		angular	0°	±°										
				www.fci.com		cat. no.	-	Product - Customer Drw				sheet 3 of 5		



ISOMETRIC VIEW
I POSITION




1-SLOT POWER MODULE FOOTPRINT
SCALE 6:1



spec ref		SEE NOTES		dr		Jim Swain		2009/07/23		projection		size		scale		
tolerance std		TOLERANCES UNLESS OTHERWISE SPECIFIED		eng		Lin-Soe Ngwe		2012/11/19				A2		4:1		
ASME Y14.5				chr		-		-				ecn no		-		
				appr		Chen-Hong Tan		2012/11/19		product family		XCede		Released		
surface			linear				MODULE ASSEMBLY, POWER		XCede 4-PAIR BP VERTICAL, STANDARD PROFILE		dwg no		10091830		rev	
			0.X ±0.25													
			0.XX ±0.13													
ASME Y14.5			0.XXX ±													
			angular 0° ±		www.fci.com		cat. no.		SEE P/N TABLE		Product-		Customer Drw		sheet 4 of 5	


NOTES:

1. CONNECTOR MATERIALS:
HOUSING: HIGH-TEMP THERMOPLASTIC, BLACK, UL94V-0
CONTACTS: HIGH PERFORMANCE COPPER ALLOY
2. CONTACT PLATING:
SEPARABLE INTERFACE:
PERFORMANCE -BASED PLATING, QUALIFIED TO MEET THE
REQUIREMENTS OF FCI PRODUCT SPECIFICATION GS-12-0989,
INCLUDING TELCORDIA GR-1217-CORE (NOVEMBER 1995)
CENTRAL OFFICE TEST SEQUENCE.
PRESS FIT TAILS: TIN OR TIN-LEAD ON TAILS, NICKEL UNDERPLATE
3. EACH POWER CONTACT BLADE HAS TWO COMPLIANT PINS
4. THE MODULES SHOWN ON THIS DRAWING MATE WITH FCI DAUGHTERCARD
POWER MODULE P/N 10091828-XXX
5. "2-SLOT" AND "3-SLOT" MODULES WILL ACCEPT DC ENDCAPS BETWEEN DC
POWER MODULES WITH NO ADDITIONAL SPACE REQUIREMENTS.
6. WHEN USING ENDCAPS BETWEEN SIGNAL WAFERS AND DC POWER MODULES,
ADD 1.85mm BETWEEN MODULES FOR EACH ENDCAP
7. FOR EACH ADDITIONAL POWER MODULE, ADD 5.55mm FOR "1-SLOT" MODULES,
12.95mm FOR "2-SLOT" MODULES, AND 20.35mm FOR "3-SLOT" MODULES.
8. PRODUCT SPECIFICATION: GS-12-0989
9. APPLICATION SPECIFICATION: GS-20-0342
10. NO SURFACE TRACES IN KEEP-OUT ZONE
11. PART MARKING, (PART NUMBER, LOT CODE), ON THIS SURFACE.
12. LEAD-FREE PRODUCT MEETS THE EUROPEAN UNION DIRECTIVES AND OTHER
COUNTRY REGULATIONS AS DESCRIBED IN FCI SPECIFICATION GS-22-008.
13. PACKAGING MEETS FCI SPECIFICATION GS-14-920 FOR LEAD FREE LABELLING.
14. A  SYMBOL WILL BE NEXT TO ANY DIMENSION, VIEW OR NOTE WHICH HAS BEEN MODIFIED
WITH THE CURRENT DRAWING REVISION.



DETAIL A
3-SLOT POWER MODULE FOOTPRINT
SCALE 6:1



spec ref	SEE NOTES	dr	Jim Swain	2009/07/23	projection	mm	size	A2	scale	4:1
tolerance std	TOLERANCES UNLESS OTHERWISE SPECIFIED	eng	Lin-Soe Ngwe	2012/11/19		mm	A2	4:1	ecn no	-
ASME Y14.5		chr	-	-						
		appr	Chen-Hong Tan	2012/11/19						
surface	linear	0.X	±0.25		product family	XCede	rel level	Released	dwg no	10091830
		0.XX	±0.13		MODULE ASSEMBLY, POWER		rev		A	
		0.XXX	±		XCede 4-PAIR BP VERTICAL, STANDARD PROFILE					
ASME Y14.5	angular	0°	±°		www.fci.com	cat. no.	SEE P/N TABLE	Product - Customer Drw	sheet 5 of 5	