





Mating Cycles	500
Capacitance	47pf±20%
Working Voltage	100v
Current Rating	7.5A
Insulation Resistance	>1GΩ

FREQUENCY (MHz)	ATTENUATION (dB)
5	-
10	-
50	-
100	-
500	30dB
1000	35dB

[illegible]

				Dat.	Name	 All Dim. in mm Orig. Size DIN A
			Detail.	8 - JUL - 02	CV	
			Insp.			
			Stand.			
31897	17/05/04	AF	HARTING EURL F-95972 Paris			
31058	8 - JUL - 02	CV				
Mod.	Dat.	Name				



 All Dim. in mm
 Orig. Size DIN A 4

D-Sub, female, angled,
15 Poles, with turned
solder pin , nut and
board lock

$$\frac{M_{\text{a}} M_{\text{s}} \text{lab}}{\text{Scale}}$$

1.5:1

HARTING EURL
F-95972 Paris



TB 0964214721x

Blatt/ Page

$$\frac{1}{L}$$