
PRODUCT DETAILS

PRODUCT DETAILS

Buy Now

IMSA-9257S-13Y935 （Product number (Product)： IMSA-9257S-13H-TS1）



Download Documents
Please check 3D data and drawings after Login/Create Account .

IMSA-9257S-13Y935 Inquire About

Inquiries About Products

Make a Sample Request

Purchase on EC site

* Request for ordering

Products

Product number (Packaging)	IMSA-9257S-13Y935	Product number (Product)	IMSA-9257S-13H-TS1
Category	Socket Connectors	Series	9257S

Specifications

Connecting Type	Socket	PCB Mounting Methods	SMT
Mating Interface	Stacking	Connector Orientation	Vertical
Contact Direction		Mating Direction	TopEntry
[illegible] Pitch		Solder Tail Pitch	2 Pitch
Pin Counts	13 Pin	Contact Plating	Tin
Plating Thickness	3 μm Min.	Signal Spec	
Signal Transmission Speed		Length (Pitch Direction)	32.8 mm
Width (Depth)	4.7 mm	Height	8 mm
Rated Voltage (AC)	125 V	Rated Voltage (DC)	125 V
Rated Current	1 A	Withstand Voltage	1000 V（AC）
Impedance Matching		Contact Resistance	100 mΩ Max.
Operating Temperature Range (Max.)	105 °C	Operating Temperature Range (Min.)	-40 °C
Array	Single Row	RoHS2	Yes
Halogen Free	Yes	Floating	

This website uses cookies for the purpose of improving customer convenience and maintaining and improving the quality of services.
By continuing to browse this website, you agree to our use of cookies. For more information, please review the Cookie Policy of this website.

Agree

Downloaded from Arrow.com.

Halogen Free	Yes
2-Point Contact	
Cap	No
X-Axis Floating Range	0.8
Effective Wiping Length	0.8
Durability	10
Package Quantity	350

Floating	
Boss Locator	Yes
Tape	No
Y-Axis Floating Range	0.5
Amplitude	
Packaging Type	Emboss

List of products in the same series

Display Option List

	Socket Connectors	9257S	6	2	SMT	Stacking	8
	Socket Connectors	9257S	8	2	SMT	Stacking	8
	Socket Connectors	9257S	8	2	SMT	Stacking	8
	Socket Connectors	9257S	12	2	SMT	Stacking	8

See More

Product Application Examples



Head-Up Display



CID (Center Information Display)



Home Appliance

Downloaded from Arrow.com.



Communication Robot



Surveillance Camera



Pachinko (Japanese Pinball)



POS System



Barcode Reader

Notes

1: Before using our website
If you consider or order our products from our website, please do so after you have confirmed and approved the terms of use(**https://www.irisoele.com/en/website/**) and the following notes for using the website.

2: Notes for product descriptions
All data categories (product drawings, specifications, packaging specifications, catalogs, etc.) on this website are reference values. They may be changed without notice (including specification change, discontinuation of manufacturing, etc.). When considering or ordering any of the listed products, please contact our sales representative in advance and exchange "delivery specifications".

3: Please install protection circuits and redundant circuits on the PCB design to ensure the safety of the equipment and confirm the compatibility with our products.

4: This product is not intended for use with equipment and devices related to human life such as medical equipment and devices, nuclear equipment and devices, aerospace equipment and devices, transportation equipment, and equipment and devices which require a high standard of reliability. If you are considering using our products for these purposes, please be sure to check with Our Company in advance as you will need to confirm the specifications that suit your application.
Without checking with our company in advance, we assume no responsibility if this product is used for the control systems of these types of equipment and devices and if any injury or fire occurs due to failure of the product. Our Company prohibits users from purchasing or using this product for the purpose of installing it in a weapon system.

5: Disclaimers
IRISO is providing all design, code, or other such information "as is" without any warranty whatsoever. By providing design, code, or other such information, IRISO makes no claim or warranty that any such implementation, alone or in combinations, is free from any potential infringement or related claims. By placing an order or making a purchase, buyer accepts full responsibility for obtaining any rights buyer may require for its implementation of any such design, code, or other such information. IRISO expressly disclaims any warranty whatsoever with respect to the adequacy of any implementation of such design, code, or other such information, including, but not limited to, any warranties or representations that any implementation is free from claims of infringement and any implied warranties, including but not limited to, warranties of merchantability or fitness for a particular purpose.

Contact

Login

Information is automatically filled in based on your account information (you can make inquiry without log in too)

Subject Any

About IMSA-9257S-13Y935

Content of Inquiry Required

Mail address Required

info@example.com

Market Required

- Automotive Market
- Consumer Market
- Industrial Market

Downloaded from Arrow.com.

Full Name (First and Last Name) Required	First name Taro Last name Iriso
Company Name Required	Sample Inc.
Department Name Required	Sales Department
Address Required	Please select
Address2 Any	0-0-0 Marunouchi Sample Tower 101, Marunouchi, Chiyoda-ku
Position Any	Please select
Occupation Any	Please select
Phone Number Any	00000000 No Hyphens Required
E-mail Magazine Any	☑ To receive the latest event and technical news, please check the checkbox. If you want to unsubscribe, please uncheck the checkbox.
Privacy Policy Required	Privacy Policy 1. Recognizing the importance of personal information, IRISO ELECTRONICS CO., LTD. (hereinafter ,"Company") shall endeavor to appropriately treat and protect personal information of customers, shareholders, and employees (including job applicants to the Company and those who have left the Company) (hereinafter referred to as the "Customers, etc.") in accordance with the following privacy ☐ By checking this checkbox, I agree to the handling of personal information.

Send

Downloaded from Arrow.com.

Copyright IRISO Electronics Co.,Ltd. All Rights Reserved.

Downloaded from Arrow.com.