





IEEE1355 CABLING



J1	Wire color	J2
2-e	Brown	1-a
1-e	Blue	2-a
2-d	Red	1-b
1-d	Green	2-b
2-c	Black	2-c
1-c	White	1-c
2-b	Orange	1-d
1-b	Yellow	2-d
2-a	Violet	1-e
1-a	Grey	2-e
Shell	Braid	Shell

NOTES /

- MECHANICAL REQUIREMENTS
 - OPERATING TEMPERATURE = -20° TO +80°C
 - MATING CYCLES : 250, PERFORMANCE LEVEL 2 (IEC 60512-5)
- THE CONNECTOR COMPLIES REQUIREMENT : IEC 61076-4-107
- WHITE LABEL INFORMATION:

DATE CODE & LOT INFORMATION
HARTING P/N
- CABLE MUST BE PERFORMED HI-POT TEST AND CONTINUITY TEST

33 27 243 500 0018				5 m	
33 27 243 200 0017				2 m	
33 27 243 100 0016				1 m	
33 27 243 050 0015				0,5 m	
Part-No.				Dim. L	
			All Dimensions in mm Original Size DIN A 3		
			Techn. Character.		Free size tolerances
			Det.	Name	Scale /
			Detail.	06.05.08 J.S.	
			Imp.		
			Stand.		
			Har-link male DE IEEE1355 cabling double shielded cable assembly, **m		
			ZHANG HARTING LIMITED		
Mod.	Dat.	Name	TB 33 27 24x xxx 00xx		
			Sub.		
			Page /		