

May not be suitable for all medical and aerospace applications.

**Specifications: Contact Mallory Sonalert to discuss your application.**

Impedance ( $\Omega$ )	$64 \pm 15\%$ at 1000 Hz at 1.0 V
Rated Power (W)	0.1
Max Power (W)	0.2
Resonance Freq $F_o$ (Hz)	$430 \pm 20\%$ at 1.0 V
Frequency Range (Hz)	$F_o \sim 20000$
Output S.P.L. (dB)	$88 \pm 3$ at .1w/.1m 1.0k, 1.2k, 1.5k, 2.0kHz $78 \pm 3$ at 1w/1m 1.0k, 1.2k, 1.5k, 2.0kHz
Frame Material	ABS UL94 1/16"HB High Heat (BLACK)
Operating Temp	-20 to 55°C
Weight (g)	4.5
Options	For other options contact factory

**Dimensions:  $\pm 0.3$**  (units: mm)

**ROHS Compliant**

