



Part Number : [2042810100](#)

Product Description : Wi-Fi 6E Flex Cabled Side-Fed
Balanced Antenna, 100.00mm Cable Length,
Compatible with U.FL / I-PEX MHF Connectors

Series Number : 204281

Status : Active

Product Category : Antennas



Documents and Resources

Drawings

[2042810100_sd.pdf](#)

[2042810100-PK.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)


Specifications

[2042810100-AS.pdf](#)

[2042810100-PS.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains 2-Methyl-1-(4-methylthiophenyl)-2-morpholinopropan-1-one per D(2025)7771-DC (04 Feb 2026) SCIP:bc5968db-5bed-458f-8beb-659ba1c3f73d

EU RoHS

Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of ComplianceAdditional Product Compliance Information**Part Details****General**

Status	Active
Category	Antennas
Series	204281
Description	Wi-Fi 6E Flex Cabled Side-Fed Balanced Antenna, 100.00mm Cable Length, Compatible with U.FL / I-PEX MHF Connectors
Component Type	Flexible Antenna with Cable
Function	Signal
Product Name	2.4/5GHz Wi-Fi Antenna
Protocol	BLE, BT, Thread, Wi-Fi, Wireless Hart, Zigbee
Type	Internal, Wi-Fi Antenna
UPC	191128324496

Electrical

Band#1 F_End (MHz)	2483.5
Band#1 F_Start (MHz)	2400
Band#2 F_End (MHz)	5850

Band#2 F_Start (MHz)	5150
Electrical Connectivity	Cable
Peak Gain (dBi)	2.0 @ 2.4 GHz, 3.3 @ 5 GHz
Return Loss - S11 (dB)	< -10
Total Efficiency	>65% @2.4 GHz, >68% @ 5 GHz

Physical

Cable Length	100.00mm
Length	35.00mm
Mounting Style	Adhesive
Net Weight	0.668/g
Packaging Type	PET Film
Polarization	Linear
Radiation Pattern	Omnidirectional
Thickness	0.10mm
Width	11.00mm

Mates With / Use With

Mates with Part(s)

Description	Part Number
MCRF Jack, Straight, PCB Receptacle, Surface Mount, 1.25mm Mounted Height, 50 Ohms	<u>734120110</u>

This document was generated on Apr 12, 2026