

## Protect It! Surge Protector with 6 Right-Angle Outlets, 6 ft. (1.83 m) Cord, 1340 Joules, Diagnostic LEDs, Metal Case

MODEL NUMBER: **TLM626**



### Highlights

- 6 outlets / 6-ft. (1.83 m) cord
- 1340 joule rating
- Rugged metal case

### Package Includes

- TLM626 surge suppressor
- Instruction manual and warranty information

### Description

The TLM626 surge suppressor offers complete AC surge suppression for comprehensive protection of workstations, personal computers, home stereos, televisions, VCRs, DVD players and other sensitive electronics. Heavy-grade AC surge suppression shields connected equipment from damage and performance problems due to transient surges. TLM626 offers six right-angle outlets, a six-foot (1.8 meters) power cord and diagnostic LEDs to warn of wiring problems and suppressor damage. AC surge suppression rated at 1340 joules shields equipment from surges and line noise. Rugged metal housing with two designated transformer plug outlets offers convenient protection of desktop computer equipment and accessories.

### Features

- 6 right-angle outlets
- 6-ft. (1.83 m) cord
- Surge suppression rating: 1340 joules
- EMI/RFI noise filtering
- 15 amp resettable circuit breaker protects against overload
- Diagnostic LEDs confirm suppressor "protection present" (green) and "grounded" (red) status
- Convenient keyhole slots allow secure mounting on wall or desk
- Can accommodate up to 2 transformers without blocking adjacent outlets
- Rugged metal case provides extra safety and durability
- Illuminated power switch
- \$75,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only) covers connected equipment
- Automatic shutoff permanently cuts power to outlets if protection circuit is incapacitated, preventing equipment damage and indicating replacement is required

## Specifications

### OVERVIEW



Powering Business Worldwide

TRIPP LITE  
SERIES

UPC Code	037332132291
<b>INPUT</b>	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V (110-125V)
Input Cord Gauge Type	14 gauge; SJT
Input Cord Gauge (AWG)	14
Voltage Compatibility (VAC)	120
Maximum Surge Amps	60000
Input Plug Type	NEMA 5-15P
Input Cord Details	SJT
Input Cord Length (ft.)	6
Right-Angle Plug	No
Input Cord Length (m)	1.83
Integrated Cord Clip	No
<b>OUTPUT</b>	
Frequency Compatibility	50 / 60 Hz
Output (Watts)	1800
Output Receptacles	(6) 5-15R
Circuit Breaker (amps)	15
Overload Protection	15A resettable combo switch / circuit breaker
Transformer Accommodation	(4) Yes
Outlet Orientation	Single row of outlets
Right-Angle Outlets	Yes
<b>USER INTERFACE, ALERTS &amp; CONTROLS</b>	
Diagnostic LED(s)	Yes
Switches	Combination AC circuit breaker and 2 position on/off power switch
Diagnostic LED Details	Built-in LEDs confirm suppressor "protection present" (green) and "grounded" (red) status
<b>SURGE / NOISE SUPPRESSION</b>	
AC Suppression Joule Rating	1340
AC Suppression Response Time	< 1 ns
Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line suppression
UL1449 Let Through Rating	400V
EMI / RFI Filtering	Up to 20 dB



Powering Business Worldwide

TRIPP LITE  
SERIES

Automatic Shut-Off	Yes
<b>DATALINE SURGE SUPPRESSION</b>	
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
Telephone/DSL Protection	No
<b>PHYSICAL</b>	
Material of Construction	Metal
Power Cord Color	Black
Form Factors Supported	Supports floor / wall / desktop placement
Housing Color	Light Gray
Mounting Holes or Slots	Yes
Slot or Hole Mount Measurement (Center to Center)	225 mm
Outlets Measurement (Center to Center)	Distance between standard outlets = 30.40mm; Distance between transformer and standard outlets = 45mm
Receptacle Color	Light gray
Shipping Dimensions (hwd / in.)	12.00 x 4.60 x 2.50
Shipping Dimensions (hwd / cm)	30.48 x 11.68 x 6.35
Shipping Weight (lbs.)	1.60
Shipping Weight (kg)	0.73
Unit Dimensions (hwd / in.)	1.500 x 12.250 x 2.250
Unit Dimensions (hwd / cm)	3.8 x 31.1 x 5.7
Unit Weight (lbs.)	1.8
Unit Weight (kg)	0.82
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	32° to 104°F (0° to 40°C)
Storage Temperature Range	5° to 104°F (-15° to 40°C)
Operating Humidity Range	20% to 85% RH
Storage Humidity Range	0% to 90% RH
<b>FEATURES &amp; SPECIFICATIONS</b>	
Rotatable Outlets	No
Antimicrobial	No
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Certifications	cUL Listed; UL 1449; UL 1363; UL Listed



Powering Business Worldwide

TRIPP LITE  
SERIES

Product Compliance	RoHS
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$75,000 <a class="insuranceLink" href="//tripplite.eaton.com/support/insurance-policy">Ultimate Lifetime Insurance</a>

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.