


Data Sheet | Item Number: 773-104

PUSH WIRE® connector for junction boxes; for solid and stranded conductors; max. 2.5 mm²; 4-conductor; transparent housing; orange cover; Surrounding air temperature: max 60°C; 2,50 mm²; transparent

<https://www.wago.com/773-104>



Color: ☐ transparent



Dimensions in mm

Push wire® splicing connector, 773 Series, PUSH WIRE®

Seamless electrical installations are guaranteed with push wire® splicing connector (item number 773-104). The 773 Series PUSH WIRE® connectors for junction boxes provide safe, quick, and easy installations in any building, no matter the position or location. Conductors can only be connected to push wire® splicing connector if their strip length is 12 mm . This splicing connector has a rated voltage of 400 V and can handle currents up to 24 A, making it ideal for high-load applications. Featuring conductor terminals along with PUSH WIRE®, this connector delivers reliable performance. Our reliable PUSH WIRE® connection offers the fastest method for clamping conductors. It utilizes the conductor's stiffness to overcome the clamping spring's contact force. Dimensions: (13 x 13.1 x 19.5) mm (width x height x depth). Push wire® splicing connector is suitable for conductor cross sections ranging from 0.75 mm² to 2.5 mm².

Tin is used for coating the contact surfaces.

Notes	
General safety information	NOTICE: Observe installation and safety instructions! ▪ Only to be used by electricians! ▪ Do not work under voltage/load! ▪ Use only for proper use! ▪ Observe national regulations/standards/guidelines! ▪ Observe technical specifications for the products! ▪ Observe the number of permissible potentials! ▪ Do not use damaged/dirty components! ▪ Observe conductor types, cross-sections and strip lengths! ▪ Insert conductor until it hits the product's backstop! ▪ Use original accessories!
Safety Information	To be sold only with installation instructions! in grounded power lines



Electrical data			
Ratings per		IEC/EN 60664-1	
Overvoltage category	III	III	II
Pollution degree	3	2	2
Nominal voltage	-	-	400 V
Rated impulse withstand voltage	-	-	4 kV
Rated current	-	-	24 A

General information	
Wiring direction	Side-entry wiring

Connection Data			
Clamping units	4	Connection 1	
Total number of potentials	1	Connection technology	PUSH WIRE®
		Actuation type	Push-in
		Connectable conductor materials	Copper Aluminum
		Connectable conductor materials (note)	Terminating Aluminum Conductors (not for use in North America) WAGO Spring-Clamp Terminal Blocks are also suitable for solid aluminum conductors up to 4 mm²/12 AWG if WAGO Aluminum Contact Paste 249-130 is used for termination. Aluminum Contact Paste Advantages: ▪ Automatically destroys the oxide film during clamping. ▪ Prevents fresh oxidation at the clamping point. ▪ Prevents electrolytic corrosion between aluminum and copper conductors (in the same terminal block). ▪ Provides long-term protection against corrosion. For spring pressure connections with PUSH WIRE® connection technology, WAGO recommends that the aluminum conductor first be cleaned and then immediately inserted into the clamping unit filled with aluminum contact paste. It is also possible to apply WAGO Aluminum Contact Paste additionally on the whole surface of the aluminum conductor before termination. Please note that the nominal currents must be adapted to the reduced conductivity of the aluminum conductors:: 2.5 mm² = 16 A 4 mm² = 22 A
		Solid conductor	0.75 ... 2.5 mm² / 18 ... 12 AWG
		Stranded conductor	1.5 ... 2.5 mm² / 16 ... 12 AWG
		Note (conductor cross-section)	When using conductors of the same diameter, 0.75 mm²/18 AWG cross-section is also possible.
		Strip length	12 mm / 0.47 inches
		Wiring direction	Side-entry wiring



Physical data		
Width		13 mm / 0.512 inches
Height		13.1 mm / 0.516 inches
Depth		19.5 mm / 0.768 inches

Material data		
Note (material data)		Information on material specifications can be found here
Color		transparent
Cover color		orange
Material group		IIIa
Insulation material (main housing)		Polycarbonate (PC)
Flammability class per UL94		V2
Clamping spring material		Chrome-nickel spring steel (CrNi)
Contact material		Electrolytic copper (E _{Cu})
Contact Plating		Tin
Fire load		0.056 MJ
Weight		2.5 g

Environmental requirements		
Ambient temperature (operation)		+60 °C
Continuous operating temperature		105 °C

Commercial data		
Product Group		7 (Push Wire Conn.)
PU (SPU)		1000 (100) pcs
Packaging type		Box
Country of origin		CN
GTIN		4044918397629
Customs tariff number		85369010000

Product Classification		
UNSPSC		39121409
eCl@ss 10.0		27-14-11-04
eCl@ss 9.0		27-14-11-04
ETIM 9.0		EC000446
ETIM 10.0		EC000446
ECCN		NO US CLASSIFICATION

Environmental Product Compliance		
RoHS Compliance Status		Compliant, No Exemption



Approvals / Certificates

General approvals



Approval	Standard	Certificate Name
CCA UL International Demko A/S	EN 60998	CCA-DK No. 2520
CSA DEKRA Certification B.V.	C22.2	15411 (LR46759)
DEMKO UL International Demko A/S	EN 60998	D-10520
ÖVE Österreichischer Verband für Elektrotechnik	EN 60998	1193-031-09
UL UL International Germany GmbH	UL 486C	E69654

Declarations of conformity and manufacturer's declarations

Approval	Standard	Certificate Name
EU-Declaration of Conformity WAGO GmbH & Co. KG	-	-
UK-Declaration of Conformity WAGO GmbH & Co. KG	-	-

Approvals for marine applications



Approval	Standard	Certificate Name
ABS American Bureau of Shipping	-	23-2417173-PDA
BV Bureau Veritas S.A.	EN 60998	11914/E0 BV
LR Lloyds Register	EN 60998	LR2446364TA
PRS Polski Rejestr Statków	EN 60998	TE/1093/880590/23

Downloads

Environmental Product Compliance

Compliance Search
Environmental Product Compliance 773-104



CAD/CAE-Data

CAE data
WSCAD Universe 773-104





1 Compatible Products

1.1 Optional Accessories

1.1.1 Mounting adapter

1.1.1.1 Mounting accessories



Item No.: 773-332
Mounting carrier; 773 Series - 2.5 mm² / 4 mm² / 6 mm²; for DIN-35 rail mounting/screw mounting; orange

1.1.2 Tool

1.1.2.1 Aluminum contact paste



Item No.: 249-130
Syringe; Contents: Aluminum Contact Paste, 20 ml