

1

2

3

4

LEAD FREE PART NUMBER

DA7WS343A40LF	ø 2.8	ø 3.1
DA7WS343A40LF	ø 2.8	ø 3.1
DA7WS300A30LF	ø 2.0	ø 2.4
DA7WS343A30LF	ø 2.0	ø 2.4
PART NUMBER	ø A	ø B ± 0.1

REFERENCE SPECIFICATIONS

-NFC 93425 (in compliance with HE 507)

PHYSICAL CHARACTERISTICS

-INSULATOR MATERIAL: THERMOPLASTIC / STANDARD MATERIAL

-CONTACT MATERIAL: PHOSPHOR BRONZE(FEMALE SIGNAL CONTACT)

BRASS(PIN SIGNAL CONTACT)

BRASS (POWERS CONTACT)

-ACCESSORIES: BRASS TIN LEAD OVER NICKEL

-SHELLS: STEEL BRIGHT TIN LEAD

ELECTRICAL CHARACTERISTICS

-NOMINAL CURRENT: 7.5A (STANDARD CONDITIONS)

-CONTACT RESISTANCE: <7.3mOhm

-CONTACT/CONTACT : 1000 V

-CONTACT/GROUND : 1200 V

-INSULATION RESISTANCE: 5000 Mohm

ENVIRONMENTAL CHARACTERISTICS

- CLIMATIC CATEGORY: 55/125/21

TEMPERATURE RANGE -55°C TO +125°C


DAMP HEAT STEADY STATE 21 DAYS

SALT SPRAY 24 HOURS

NOTE ROHS INFORMATION


- The "LF" products meet european union Directives and other country regulations as described in GS-22-008.
- The housing will withstand exposure to 260°C peak temperature for 3.5 seconds in a wave solder application with a 1.6mm minimum thick circuit board. See application notes/procedures if they are available.
- Termination plating spec:
 - Signal contacts: Ni + Gold
 - Power contacts: 1.27µm Nickel mini, 2.5 to 7.5 µm Sn (pure bright)
 - Shell plating : 2 to 4µmCu + 3 to 10µmm Sn(pure bright)
 - Accessories: Sn pure bright
- Packaging spec: See GS-14-920

European Views



LAYOUT DIMENSIONS (after plating)

CONNECTOR SIDE VIEW



www.fciconnect.com

surface	ISO 1302	tolerance std	ISO 406 ISO 1101	projection	mm
tolerances UNLESS OTHERWISE SPECIFIED					

rev	ecn no	dr	date	Dr	M	PESSON	2005/12/01	ANGULAR	0.X	±0.1	size	A3	1.5
A	LS05-0106	MPE	2003/09/19	Eng	PESSON		2005/12/01	LINEAR	0.XX	±0.1	ECN	F10-0032	
B	LS06-0097	LGO	2006/07/31	Chr	LEGARE		2005/12/01	0.XX	0.XXX	±0.1	ECN	F10-0032	
C	FT0-0032	LSA	2010/04/13	Appr	LEGARE		2005/12/01	Product family	D-SUB	Spec ref	-		



SOCKET CONNECTOR WITH STR
CONTACTS AND 2 POWERS 40A

C01-8639-2322
CUSTOMER sheet 1 of 1