



Pushing Performance  
Since 1945

# Han PP RJ45 10G met. plug set 45° top



Image is for illustration purposes only. Please refer to product description.

Part number	09 35 225 0403
Specification	Han PP RJ45 10G met. plug set 45° top
HARTING eCatalogue	<a href="https://b2b.harting.com/09352250403">https://b2b.harting.com/09352250403</a>

## Identification

Category	Connectors
Series	Han® PushPull (V14)
Identification	RJ45
Element	Connector sets
Features	Intuitive locking mechanism Field assembly without tools

## Version

Termination method	IDC termination
Shielding	Fully shielded, 360° shielding contact
Number of contacts	8
Version	Top entry
Locking type	PushPull
Pack contents	incl. housing and male insert

## Technical characteristics

Conductor cross-section	0.1 ... 0.32 mm² Stranded 0.1 ... 0.32 mm² Solid
Conductor cross-section	AWG 27/7 ... AWG 22/7 Stranded AWG 27/1 ... AWG 22/1 Solid
Wire outer diameter	≤1.6 mm
Rated current	1.75 A
Rated voltage	50 V
Transmission characteristics	Cat. 6 Class E <sub>A</sub> up to 500 MHz



**Pushing Performance**  
Since 1945

## Technical characteristics

Data rate	10 Mbit/s
	100 Mbit/s
	1 Gbit/s
	2.5 Gbit/s
	5 Gbit/s
	10 Gbit/s
Limiting temperature	-40 ... +70 °C
Mating cycles	≥750
Degree of protection acc. to IEC 60529	IP65
	IP67
Clamping range	6.5 ... 9.5 mm

## Material properties

Surface (contacts)	Au over Ni Mating side
	Sn over Ni Termination side
Material (hood/housing)	Zinc die-cast
Surface (hood/housing)	Nickel plated
Material (O-ring)	NBR
Material (cable seal)	TPE
Material flammability class acc. to UL 94	V-0
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
	2-methyl-1-(4-methylthiophenyl)-2-morpholinopropan-1-one
California Proposition 65 substances	Yes
California Proposition 65 substances	Antimony trioxide
	Lead
	Nickel

## Specifications and approvals

Specifications	IEC 61076-3-117 Variant 14 (V14)
	IEC 60603-7 Mating face
	EN 45545-2



Pushing Performance  
Since 1945

Specifications and approvals

UL / CSA	UL 1977 ECBT2.E102079 CSA-C22.2 No. 182.3 ECBT8.E102079
Approvals	DNV GL
PROFINET	Yes

Commercial data

Packaging size	10
Net weight	37.78 g
Country of origin	Romania
European customs tariff number	85366990
GTIN	5713140054059
ETIM	EC002636
eCl@ss	27440114 Rectangular connector (for field assembly)