




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A1	ECR-20-004655	29SEP2020	RK	SBH




1. PACKAGING ACC. TO TE SPEC.107-18032
BUNDLE EVERY 25 ASSEMBLIES WITH A RUBBER BAND
2. ELECTRICAL TEST CONTAINING "SHORT CIRCUIT TEST, CONTINUITY
AND ACCURATE CAVITY ASSIGNMENT TEST" ACC. TO
TE-SPEC.108-18857, SUBSECTION 3.1.1

3 WIRING SCHEDULE AS SHOWN

WIRING SCHEDULE		
OUTLET		SIDE
1	+	RIBBED
2	-	SMOOTH

CROSS SECTION OF SPT-2 CABLE



OBSOLETE	16.0 FT	±3.84	2181198-8
	14.0 FT	±3.36	2181198-7
	12.0 FT	±2.88	2181198-6
	10.0 FT	±2.4	2181198-5
OBSOLETE	8.0 FT	±1.92	2181198-4
	6.0 FT	±1.44	2181198-3
	4.0 FT	±.96	2181198-2
	2.0 FT	±.48	2181198-1
	"L"	TOLERANCES [INCHES]	TE P/N

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN E.C. CLAYBAUGH 16/JUN/11		 TE Connectivity			
		CHK P. BECKER 13/JUL/11					
DIMENSIONS: INCHES		TOLERANCES, UNLESS OTHERWISE SPECIFIED:		NAME CABLE ASSY, NECTOR, LV-2, OUTLET – PIGTAIL			
		0 PLC ± -					
		1 PLC ± -					
		2 PLC ± -		-			
		3 PLC ± -		-			
		4 PLC ± -		-			
MATERIAL		FINISH		PRODUCT SPEC		RESTRICTED TO	
-		-		-		-	
				APPLICATION SPEC			
				-			
				WEIGHT		-	
				-			
CUSTOMER DRAWING				SIZE	CAGE CODE	DRAWING NO	
				A2	00779	C=2181198	
				SCALE		SHEET	REV
				N.T.S.		1 of 1	A1