




## Features

- 5 x 3 x 1.5 Inches Form factor
- Up to 550 Watts with Forced Air Cooled
- Efficiencies up to 92%
- -40 to 70 degree operating temperature\*
- 12V / 0.5A Fan Output
- Thermal Shut-Down feature
- Shall be approved to EN60601-1 3rd Edition
- Meets EN60601-1-2, 4<sup>th</sup> Edition
- Medical (BF) Safety Approvals
- MTBF : >3M hours as per Telcordia SR-332, issue 3

## Electrical Specifications

|                              |                                                                                                                                       |                                 |                                |
|------------------------------|---------------------------------------------------------------------------------------------------------------------------------------|---------------------------------|--------------------------------|
| Input Voltage                | 90-264 VAC/390 VDC, Universal (Derate from 100% at 115VAC to 78% at 90VAC)                                                            |                                 |                                |
| Input Frequency              | 47-63 Hz                                                                                                                              |                                 |                                |
| Input Current                | 115 VAC: 6.0 A max.                                                                                                                   | 230 VAC: 3.0 A max.             |                                |
| No Load Power                | < 0.5W @ 115VAC                                                                                                                       |                                 | < 0.7W @ 230VAC                |
| Inrush Current               | 115 VAC – 25 A, 230 VAC – 45 A, 264 VAC – 75 A                                                                                        |                                 |                                |
| Leakage Current              | <200uA @115VAC and <400uA @230VAC                                                                                                     |                                 | Touch current <100uA           |
| Efficiency                   | 92%(48V), 91%(24V), 90%(12V,15V) typical @ 230VAC full load                                                                           |                                 |                                |
| Hold-up Time                 | Full Load > 16 ms typical                                                                                                             | Convection Load > 55 ms typical | Conduction Load > 30ms typical |
| Power Factor                 | exceeds 0.95 with Full Load                                                                                                           |                                 |                                |
| Output Power                 | up to 550W (Forced Air Cooled)<br>up to 250W (Conduction Cooled)<br>up to 150W (Convection Cooled)                                    |                                 |                                |
| Output Voltage Adjustability | +/-3%                                                                                                                                 |                                 |                                |
| Line Regulation              | +/-0.5%                                                                                                                               |                                 |                                |
| Load Regulation              | +/-1%                                                                                                                                 |                                 |                                |
| Transient Response           | 50-100% step load change, at 0.1A/uS slew rate, 50% duty cycle, 50Hz=5% ,<br>recovery time < 5 ms                                     |                                 |                                |
| Rise Time                    | 55 ms typical                                                                                                                         |                                 |                                |
| Set Point Tolerance          | +/-1%                                                                                                                                 |                                 |                                |
| Over Current Protection      | >110%, Hiccup mode / Auto Recovery                                                                                                    |                                 |                                |
| Over Voltage Protection      | 110 to 140%, Hiccup mode / Auto Recovery                                                                                              |                                 |                                |
| Short Circuit Protection     | Hiccup mode / Auto Recovery                                                                                                           |                                 |                                |
| Switching Frequency          | PFC – 70 to 130 KHz ,Resonant – 68 to 80 KHz                                                                                          |                                 |                                |
| Operating Temperature        | -40 to +70°C, * -40 to 0°C startup is guaranteed with spec deviation ( ref note 6)                                                    |                                 |                                |
| Storage Temperature          | -40 to +85°C                                                                                                                          |                                 |                                |
| Relative Humidity            | 5% to 95%, noncondensing                                                                                                              |                                 |                                |
| Altitude                     | Operating: 16,000 ft.; Nonoperating: 40,000 ft.                                                                                       |                                 |                                |
| Isolation Voltage            | Input to Output – 4000 VAC medical applications.<br>Input to GND - 1500 VAC , Output to GND- 1500VAC for type BF , 500 VAC for type B |                                 |                                |

| Model Number | Voltage | Max. Load<br>(Convection) | Max. Load <sup>7</sup><br>(Conduction) | Max. Load<br>(400 LFM) | Min. Load | Ripple <sup>1</sup> |
|--------------|---------|---------------------------|----------------------------------------|------------------------|-----------|---------------------|
| MWLC550-1012 | 12V     | 9.17A                     | 16.67A                                 | 41.67A                 | 0.0A      | 2%                  |
| MWLC550-1015 | 15V     | 7.33A                     | 13.33A                                 | 33.33A                 | 0.0A      | 2%                  |
| MWLC550-1024 | 24V     | 6.25A                     | 10.42A                                 | 22.92A                 | 0.0A      | 1%                  |
| MWLC550-1030 | 30V     | 5.00A                     | 8.33A                                  | 18.33A                 | 0.0A      | 1%                  |
| MWLC550-1048 | 48V     | 3.13A                     | 5.21A                                  | 11.46A                 | 0.0A      | 1%                  |
| MWLC550-1058 | 58V     | 2.59A                     | 4.31A                                  | 9.48A                  | 0.0A      | 1%                  |

| Connectors |       |            |
|------------|-------|------------|
| J1         | Pin 1 | AC LINE    |
|            | Pin 2 | NOT FITTED |
|            | Pin 3 | AC NEUTRAL |
| J2         | Pin 1 | V1 +VE     |
|            | Pin 2 | V1 -VE     |
| J3         | Pin 1 | FAN +VE    |
|            | Pin 2 | FAN -VE    |

## Notes

1. Ripple is peak to peak with 20 MHz bandwidth and 10  $\mu$ F (Electrolytic capacitor) in parallel with a 0.1  $\mu$ F capacitor at rated line voltage and load ranges.
2. Combined output power of main output, fan supply shall not exceed max. Power rating.
3. Fan supply output voltage tolerance including set point accuracy, line and load regulation is +/-10% and Ripple and noise is less than 10%.
4. Specifications are for nominal input voltage, 25°C unless otherwise stated.
5. Thermal shutdown feature : The power supply goes in hiccup mode when the temperature of Substrate PCB exceeds 110 °C (+/-10 °C).
6. Output ripple can be more than 10% of the output voltage.
7. Refer Recommended Conduction Plate & Clearance on Page No. 6



Innovations in Power

## Mechanical Specifications

|                                              |                                                                                                                                                                                                                                                                                                    |
|----------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| AC Input Connector (J1)                      | JST : B3P-VH-B(LF)(SN) or equivalent<br>Mating: VHR-3M or equivalent Pins : SVH-41T-P1.1 or equivalent                                                                                                                                                                                             |
| Earth (J4)                                   | Molex: 19705-4301<br>Mating: 19003-0001                                                                                                                                                                                                                                                            |
| DC Output Connector (J2)<br>(Screw Terminal) | 6-32 inches Screw Pan HD<br>Mating: Designed to accept Ring Tongue Terminal AMP : 8-31886-1,<br>wherein one 16 AWG(max) wire can be crimped.<br>Note : One Ring Tongue Terminal with 16 AWG is recommended for current up to 11A only.<br>Use multiple tongue terminals with wire for more current |
| Aux (Fan) Output(J3)                         | AMP :640456-2<br>Mating: 640440-2                                                                                                                                                                                                                                                                  |
| Dimensions                                   | 5 x 3 x 1.5 inches<br>(127 x 76.2x 38.1 mm)                                                                                                                                                                                                                                                        |
| Weight                                       | 500 gm approx                                                                                                                                                                                                                                                                                      |

## EMC


| Parameter                          | Conditions/Description             | Criteria                                                                        |
|------------------------------------|------------------------------------|---------------------------------------------------------------------------------|
| Conducted Emissions                | EN 55011-B,CISPR22-B, FCC PART15-B | Pass                                                                            |
| Radiated Emissions                 | EN 55011 A                         | Pass<br>Level B with external core (King core K5B RC 25x12x15-M in input cable) |
| Input Current Harmonics            | EN 61000-3-2                       | Class D                                                                         |
| Voltage Fluctuation and Flicker    | EN 61000-3-3                       | Pass                                                                            |
| ESD Immunity                       | EN 61000-4-2                       | Level 4, Criterion A                                                            |
| Radiated Field Immunity            | EN 61000-4-3                       | Level 3, Criterion A                                                            |
| Electrical Fast Transient Immunity | EN 61000-4-4                       | Level 3, Criterion A                                                            |
| Surge Immunity                     | EN 61000-4-5                       | Level 3, Criterion A                                                            |
| Conducted Immunity                 | EN 61000-4-6                       | Level 3, Criterion A                                                            |
| Magnetic Field Immunity            | EN 61000-4-8                       | Level 4, Criterion A                                                            |
| Voltage dips, interruptions        | EN 61000-4-11                      | Criterion B                                                                     |

## Safety

|                       |                                                                                                                                                                                                                                                                                        |
|-----------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| CE Mark               | Complies with LVD Directive                                                                                                                                                                                                                                                            |
| Approval Agency       | Nemko, UL, C-UL                                                                                                                                                                                                                                                                        |
| Safety Standard(s)    | UL /CSA : ANSI/AAMI ES60601-1 (2005 + C1:09 + A2:10) AMD1:2012; CORR1:2009; AMD2:2010,<br>(/ CAN/CSA-C22.2 No. 60601-1 (2008)CAN/CSA C22.2 No. 60601-1:14<br>IEC : IEC 60601-1: 2005 + CORR. 1:2006 + CORR. 2:2007 + AM1:2012(or IEC 60601-1: 2012 reprint)<br>EN : EN 60601-1:2006;A1 |
| Safety File Number(s) | UL Certificate No : E173812<br>CB Test Certificate No : NO93054<br>Nemko Certificate No : P16221240                                                                                                                                                                                    |


## Derating Curve

### Power De-rating : w.r.t. Input For all mounting options a to f



De-rate linearly from 100% at 115VAC to 78% at 90VAC

### Power De-rating : 12V, 15V For all mounting options a to f




Convection load: 110W up to 50 °C  
De-rate above 50 °C @ 2.5% per °C

Conduction load: 200W up to 50 °C  
De-rate above 50 °C @ 2.5% per °C

Forced air cooled load : 500W up to 50°C  
De-rate above 50 °C @ 2.5% per °C

### Power De-rating : 24V, 30V, 48V, 58V For all mounting options a to f



Convection load: 150W up to 50 °C  
De-rate above 50 °C @ 2.5% per °C

Conduction load: 250W up to 50 °C  
De-rate above 50 °C @ 2.5% per °C


Forced air cooled load : 550W up to 50°C  
De-rate above 50 °C @ 2.5% per °C




Innovations in Power

## Maximum Operating Temperature

For reliable and safe operation, please make sure the maximum component temperatures given in table below is not exceeded.



TOP PCB






BOTTOM PCB

| Ident no | Description           | Max Temp Allowed (°C)                            |
|----------|-----------------------|--------------------------------------------------|
| 1        | Common mode chokes    | 95                                               |
| 2        | Input Bulk Capacitors | 90                                               |
| 3        | Differential choke    | 110                                              |
| 4        | Boost Choke           | 110                                              |
| 5        | Output Transformer    | 125 (for 12V & 15V)<br>110 (for 24V,30V,48V,58V) |
| 6        | Output Capacitor      | 90                                               |
| 7        | Bridge Rectifier      | 120                                              |
| 8        | Aluminium Clad PCB    | 105                                              |
| 9        | Output Rectifiers     | 110                                              |


## Recommended Conduction Plate & Clearance

Conduction power rating mentioned in the table is with additional aluminium base plate of 3 mm thickness with 177.8mm(7in) length & 101.6mm(4in) width.


Clearance of minimum 15mm above the component height is recommended for better thermal management.




## Mounting Option




### FIXING OPTION - 1



### FIXING OPTION - 2



## Mechanical Drawing



Innovations in Power