



MK-0001-35-SCL-TBG-PKG Product Details

[Share](#) [Print](#) [Email](#)

Active

Heat Shrink Tubing

MK-0001-35

MK-0001-35-SCL-TBG-PKG

TE Internal Number: 975269-000

Product Highlights [View All](#)

- Heat Shrinkable Tubing
- Product Name = SCL
- Product Source = U.S.
- Semirigid
- Medium Wall Style

[Pricing & Availability](#)
[Request Sample](#)
[Add to My Part List](#)
[Buy Product through Distributor](#)
[Feedback](#)
[Documents](#) [Features](#) [Compliance](#)
Please Note:
 Use the Product Drawing for all design activity

Product Type Features

Product Type	Heat Shrinkable Tubing
Color	Blue
Sealant	With

Mechanical Attachment

Adhesive	Yes
----------	-----

Dimensions

Inside Diameter (Min-Max) (mm [in])	4.75 – 9.53 [0.187 – 0.375]
Expanded ID, Min. (mm [in])	6.40 [0.252]
Recovered ID, Max. (mm [in])	5.00 [0.197]
Length (mm [in])	101.60 [4.000]
Cut Length (mm [in])	101.60 [4.000]

Body Features

Product Name	SCL
Pliancy	Semirigid
Wall Style	Medium
Wall Type	Dual
Lining Type	Encapsulant
Material	Crosslinked Polyolefin
Shrink Ratio	3:1
Fluid Type	Aviation Fuel
Resistant To	Moisture

Housing Features

Material Systems	No
------------------	----

Configuration Features

Modification	None
--------------	------

Industry Standards

Government/Industry Qualification	No
UL Rating	Listed
Approved Standards	SAE AMS-DTL-23053/10
RoHS/ELV Compliance	Not reviewed for ELV/RoHS compliance
Lead Free Solder Processes	Not relevant for lead free process

Printer/Label Features

Voltage Rating (kV)	0.6
---------------------	-----

Environmental

Fluid Resistance	Immersion
Operating Temperature (°C)	-55 – +110

Conditions for Usage

Full Recovery Temperature (°C)	135
Shrink Temperature, Min. (°C)	135
High Temperature Compatible	No

Operation/Application

Product Use	Minor Repairs
Application	General Purpose

Packaging Features

Packaging Method	Bag/Box
------------------	---------

Product Availability

Product Source	U.S.
----------------	------

Other

Brand	Raychem
-------	---------

Related Products

Not quite the product you're looking for?

[Find Similar Products](#)
[View Part in Product Feature Selector](#)
[Check for Tooling](#)
Corporate Information
[About TE](#)
[Investors](#)
[News Room](#)
[Supplier Portal](#)
[Careers](#)
[Terms & Conditions](#)
[Privacy Policy](#)
[Global Accessibility Statement](#)
Quick Links
[Distributor Inventory](#)
[Product Cross Reference](#)
[Documents & Drawings](#)
[Product Compliance Support Center](#)
[Site Map](#)
Customer Support
[Email or Chat With Us](#)
[Find a Phone Number](#)
[Knowledge Base](#)
[Manage Your Account](#)
Keep Me Informed
