
Part Number : 2072350150
Product Description : 824MHz-2170MHz Cellular Flexible Antenna, 150.00mm Cable Length, Compatible with U.FL / I-PEX MHF Connectors
Series Number : 207235
Status : Active
Product Category : Antennas



Documents and Resources

Drawings

2072350150_sd.pdf

2072350100-PK.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Specifications

2072350100-AS.pdf

2072350100-PS.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

Downloaded from Arrow.com.

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Antennas
Series	207235
Description	824MHz-2170MHz Cellular Flexible Antenna, 150.00mm Cable Length, Compatible with U.FL / I-PEX MHF Connectors
Component Type	Flexible Antenna with Cable
Function	Signal
Product Name	Cellular Flexible Antenna
Protocol	Cellular
Type	Cellular Antenna, Internal
UPC	191128895927

Electrical

Band#1 F_End (MHz)	960
Band#1 F_Start (MHz)	824
Band#2 F_End (MHz)	2170
Band#2 F_Start (MHz)	1710
Electrical Connectivity	Cable
Peak Gain (dBi)	0 @ 824 MHz, 3.8 @ 1710 MHz
Return Loss - S11 (dB)	< -5, < -8
Total Efficiency	>31% @ 824 MHz, >60% @ 1710 MHz

Downloaded from Arrow.com.

Physical

Cable Length	150.00mm
Length	40.40mm
Mounting Style	Adhesive
Net Weight	0.791/g
Packaging Type	PET Film
Polarization	Linear
Radiation Pattern	Omnidirectional
Thickness	0.10mm
Width	15.40mm

Mates With / Use With

Mates with Part(s)

Description	Part Number
MCRF Jack, Straight, PCB Receptacle, Surface Mount, 1.25mm Mounted Height, 50 Ohms	734120110

Downloaded from Arrow.com.