




MQS

TE Internal #: 1473247-1

Cover Assembly, Cable Exit Angle 180°, Black, PBT GF, -40 – 120 °C [-40 – 248 °F], Automotive Connector Caps & Covers

[View on TE.com >](#)

Connectors > Automotive Connectors > Automotive Connector Accessories > Automotive Connector Caps & Covers



Protection & Strain Relief Accessory Type: **Cover Assembly**

Cable Exit Angle: **180°**

Strain Relief: **With**

Primary Product Color: **Black**

Primary Product Material: **PBT GF**

Features

Product Type Features

Sealable	Yes
Protection & Strain Relief Accessory Type	Cover Assembly

Body Features

Cable Exit Angle	180°
Primary Product Color	Black
Primary Product Material	PBT GF

Mechanical Attachment

Strain Relief	With
---------------	------

Usage Conditions

Operating Temperature (Max)	70 °C, 75 °C, 80 °C, 85 °C, 90 °C, 100 °C, 105 °C, 110 °C, 120 °C [158 °F][167 °F][176 °F][185 °F][194 °F][212 °F][221 °F][230 °F][248 °F]
Operating Temperature Range	-40 – 120 °C [-40 – 248 °F]

Packaging Features

Packaging Quantity	70
Packaging Method	Bag

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)



EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # CAT-M8793-CH8172
MQS, CONNECTOR HOUSING



TE Part # 1473244-3
MQS/JPT 81POS PLUG ASSY

TE Part # 1473248-1
SEALED MOS CLEANBODY/JPT 81POS

TE Part # 1473249-1
SEALED MQS CLEANBODY/JPT 81POS

Customers Also Bought



TE Part #DRC26-40SB-L011
DEUTSCH DRC Housings



TE Part #964282-2
JPT A REC 2.8 Contact SWS Sn



TE Part #5-968221-1
MQS, RECEPTACLE AND TAB




TE Part #347707-1
0.5MM CABLE SEAL HC SILIC



TE Part #2119785-7
CRIMPER, INSUL OVERLAP PREM



TE Part #7-2837090-7
OCEAN_2.0_SPARE_PART_KIT-
080F110F



TE Part #1203559-3
EXTERNAL RELAY BASE(FR)

Documents

Product Drawings

MQS 81P LEVER(R) ASSY

English

CAD Files

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_1473247-1_A.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1473247-1_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1473247-1_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English

Application Specification

English

Instruction Sheets

Instruction Sheet (non U.S.)

English



[Instruction Sheet \(non U.S.\)](#)

Japanese

[UNSEALED GET/MCP 81/40 SLIDER LEVER TYPE CONNECTOR](#)

Japanese

[Instruction Sheet \(non U.S.\)](#)

Japanese