


Multi-Device Charging Cart, 36 AC Outlets, Chromebooks and Laptops, Black

MODEL NUMBER: **CSC36AC**



Keep up to 36 Chromebooks and laptops secure, charged and ready to use. Ideal for classrooms, businesses and government organizations that rely on daily use of mobile devices.

Features

Charges 36 Chromebooks and Laptops Up to 15 in. Device power adapters plug into internal NEMA 5-15R outlets (up to 1,440 watts total) Also charges tablets and other USB devices through their power adapters Extra internal AC outlet for powering peripherals RJ45 jack for external Ethernet networking 10-ft. (3.05 m) AC input cord with NEMA 5-15P plug reaches distant outlets

Timed Device Charging to Guard Against Overloads Internal outlets split into 2 color-coded zones of 18 outlets each Timer alternates charging between zones hourly LEDs indicate which zone is being charged

Dual External AC Outlets NEMA 5-15R outlets for connecting projectors and other devices Can be switched on and off to protect against possible overloads

Comprehensive Protection Devices and adapters kept in separate, lockable compartments Doors lock with included keys to help prevent theft, damage and tampering Flow-through ventilation helps prevent overheating Circuit breaker protects against overloads Heavy-duty steel construction and powder-coated finish promote long-term durability

Clutter-Reducing Organization Heavy power adapters store out of the way in removable rear baskets Cables and connectors run through shelf slots and overhead cable manager Device spaces numbered for easy identification

Simple Mobility Locking swivel casters with non-marking wheels for smooth, even ride Reversible wide-grip handle assists cart control Power cord wrap keeps input cord out of the way Corner safety bumpers prevent scratches on walls and doorways Compact cart fits in same space as typical AV cart

Flexible Configuration Ships ready for quick, easy installation—just attach handle, bumpers and cord wrap Adjustable dividers accommodate up to 12 devices per shelf Laminated wood-grain top serves as a smooth writing surface

Highlights

- Charges 36 Chromebooks and laptops with screen sizes up to 15 in.
- Hourly timer alternates charging zones to help prevent overloads
- In-cabinet RJ45 jack allows secure use of a wireless router
- Convenient external outlets provide power for a monitor or projector

Package Includes

- CSC36AC 36-Device AC Charging Station Cart, Black
- Cart handle
- Input cord wrap
- (6) Protective bumpers
- (10) Hex screws
- Hex key
- (2) Keys
- Owner's manual

Specifications

OVERVIEW	
UPC Code	037332200488
Product Type	Multi-Device Charger



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Charging Form Factor	Mobile Cart
Functions	Charge; Secure
Device Compatibility	Chromebook; Laptop
Device Slots	36
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Voltage Compatibility (VAC)	120
Input Frequency	60 Hz
Input Plug Type	NEMA 5-15P
Input Cord Length (ft.)	10
Input Cord Length (m)	3.05
CHARGING	
Number of Charging Ports	36
Charging Method	AC
Charging Port Type	NEMA 5-15R
Charging Ports Details	Pass through
Charging Ports / Amps	(36) 12A
Overcharge Protection	No
Charging Amps per Port	12A
PHYSICAL	
Color	Black
Antimicrobial Coating	No
Charging Station Form Factor	Mobile Cart
Material of Construction	Steel
Shipping Dimensions (hwd / cm)	119.00 x 68.00 x 73.99
Shipping Dimensions (hwd / in.)	46.85 x 26.77 x 29.13
Shipping Weight (kg)	85.28
Shipping Weight (lbs.)	188.00
Slot Dimensions - Bottom (hwd / in.)	10.11 x 1.5 x 15.58
Slot Dimensions - Bottom (hwd / mm)	256.9 x 38.22 x 395.72
Slot Dimensions - Middle (hwd / in.)	10.13 x 1.5 x 15.58
Slot Dimensions - Middle (hwd / mm)	257.3 x 38.22 x 395.72
Slot Dimensions - Top (hwd / in.)	10.13 x 1.5 x 15.58



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Slot Dimensions - Top (hwd / mm)	257.3 x 38.22 x 395.72
Unit Dimensions (hwd / cm)	107.45 x 71.04 x 56.13 (with handle installed)
Unit Dimensions (hwd / in.)	42.3 x 27.97 x 26.04 (with handle installed)
Unit Weight (kg)	50.00
Unit Weight (lbs.)	110.23
Number of Shelves	3
SPECIAL FEATURES	
Cord Management	Yes
EMI/RFI Line Noise Protection	No
Locking	Yes
Lock Type	Key
Built-In Circuit Breaker	Yes
Overcurrent Protection	Yes
Flow-Through Ventilation	Yes
UV Sterilization	No
STANDARDS & COMPLIANCE	
Certifications	UL 60950-1 (Power Component); CAN/CSA 22.2 No. 60950-1 (Power Component)
Approvals	RoHS
NOM (Mexico)	Tested to NOM (Mexico)
WARRANTY	
Product Warranty Period (Worldwide)	2-year limited warranty
CATEGORY PAGE FILTERS (Y/N ONLY)	
External Receptacle	Yes

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>