

MOSFET - Power, Single N-Channel, TOLL

80 V, 1.53 mΩ, 298 A

NTBLS1D5N08MC

Features

- Low $R_{DS(on)}$ to Minimize Conduction Losses
- Low Q_G and Capacitance to Minimize Driver Losses
- Lowers Switching Noise/EMI
- These Devices are Pb-Free, Halogen Free/BFR Free and are RoHS Compliant

Applications

- Power Tools, Battery Operated Vacuums
- UAV/Drones, Material Handling
- BMS/Storage, Home Automation

MAXIMUM RATINGS ($T_J = 25^\circ\text{C}$ unless otherwise noted)

Parameter		Symbol	Value	Unit
Drain-to-Source Voltage		V_{DSS}	80	V
Gate-to-Source Voltage		V_{GS}	± 20	V
Continuous Drain Current $R_{\theta JC}$ (Note 2)	Steady State	$T_C = 25^\circ\text{C}$	I_D	298 A
		$T_C = 25^\circ\text{C}$	P_D	250 W
Continuous Drain Current $R_{\theta JA}$ (Notes 1, 2)	Steady State	$T_A = 25^\circ\text{C}$	I_D	32 A
		$T_A = 25^\circ\text{C}$	P_D	2.9 W
Pulsed Drain Current	$T_A = 25^\circ\text{C}$, $t_p = 10 \mu\text{s}$	I_{DM}	4487	A
Operating Junction and Storage Temperature Range		T_J, T_{stg}	-55 to +150	°C
Source Current (Body Diode)		I_S	192	A
Single Pulse Drain-to-Source Avalanche Energy ($I_{L(pk)} = 31 \text{ A}$, $L = 3 \text{ mH}$)		E_{AS}	1441	mJ
Lead Temperature Soldering Reflow for Soldering Purposes (1/8" from case for 10 s)		T_L	260	°C


Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

THERMAL RESISTANCE MAXIMUM RATINGS

Parameter	Symbol	Value	Unit
Junction-to-Case – Steady State (Note 2)	$R_{\theta JC}$	0.5	°C/W
Junction-to-Ambient – Steady State (Note 2)	$R_{\theta JA}$	43	

1. Surface-mounted on FR4 board using a 1 in² pad size, 1 oz. Cu pad.
2. The entire application environment impacts the thermal resistance values shown, they are not constants and are only valid for the particular conditions noted.

$V_{(BR)DSS}$	$R_{DS(on)} \text{ MAX}$	$I_D \text{ MAX}$
80 V	1.53 mΩ @ 10 V	298 A
	3.7 mΩ @ 6 V	



MO-299A
TOLL
CASE 100CU

MARKING DIAGRAM



NTBLS1D5N08MC = Specific Device Code

A = Assembly Location

Y = Year

WW = Work Week

ZZ = Lot Traceability

ORDERING INFORMATION

See detailed ordering, marking and shipping information on page 5 of this data sheet.

NTBLS1D5N08MC

Table 1. ELECTRICAL CHARACTERISTICS ($T_J = 25^\circ\text{C}$ unless otherwise noted)

Parameter	Symbol	Test Conditions		Min	Typ	Max	Units
OFF CHARACTERISTICS							
Drain-to-Source Breakdown Voltage	$V_{(\text{BR})\text{DSS}}$	$I_D = 250 \mu\text{A}, V_{GS} = 0 \text{ V}$		80	—	—	V
Drain-to-Source Breakdown Voltage Temperature Coefficient	$V_{(\text{BR})\text{DSS}}/T_J$	$I_D = 250 \mu\text{A}$, ref to 25°C		—	78	—	$\text{mV}/^\circ\text{C}$
Zero Gate Voltage Drain Current	I_{DSS}	$V_{DS} = 80 \text{ V}$, $V_{GS} = 0 \text{ V}$	$T_J = 25^\circ\text{C}$	—	—	1	μA
			$T_J = 125^\circ\text{C}$	—	—	100	μA
Gate-to-Source Leakage Current	I_{GSS}	$V_{DS} = 0 \text{ V}, V_{GS} = \pm 20 \text{ V}$		—	—	± 100	nA
ON CHARACTERISTICS (Note 3)							
Gate Threshold Voltage	$V_{GS(\text{th})}$	$V_{GS} = V_{DS}, I_D = 710 \mu\text{A}$		2.0	3.0	4.0	V
Negative Threshold Temperature Coefficient	$V_{GS(\text{th})}/T_J$	$I_D = 710 \mu\text{A}$, ref to 25°C		—	-8.3	—	$\text{mV}/^\circ\text{C}$
Drain-to-Source On Resistance	$R_{DS(\text{on})}$	$V_{GS} = 10 \text{ V}, I_D = 80 \text{ A}$		—	1.30	1.53	$\text{m}\Omega$
Drain-to-Source On Resistance	$R_{DS(\text{on})}$	$V_{GS} = 6 \text{ V}, I_D = 63 \text{ A}$		—	2.0	3.7	$\text{m}\Omega$
Forward Transconductance	g_{FS}	$V_{DS} = 5 \text{ V}, I_D = 80 \text{ A}$		—	220	—	S
Gate-Resistance	R_G	$T_A = 25^\circ\text{C}$		—	0.7	—	Ω
CHARGES & CAPACITANCES							
Input Capacitance	C_{iss}	$V_{GS} = 0 \text{ V}, V_{DS} = 40 \text{ V}, f = 1 \text{ MHz}$	—	8170	—	—	pF
Output Capacitance	C_{oss}		—	3025	—	—	pF
Reverse Transfer Capacitance	C_{rss}		—	82	—	—	pF
Total Gate Charge	$Q_{\text{G}(\text{tot})}$	$V_{GS} = 10 \text{ V}, V_{DS} = 40 \text{ V}, I_D = 80 \text{ A}$	—	111	—	—	nC
Threshold Gate Charge	$Q_{\text{G}(\text{th})}$		—	22	—	—	
Gate-to-Source Charge	Q_{gs}		—	35	—	—	
Gate-to-Drain Charge	Q_{gd}		—	23	—	—	
Output Charge	Q_{oss}		—	166	—	—	
Sync Charge	Q_{sync}		—	94	—	—	
Plateau Voltage	V_P		—	5	—	—	V
SWITCHING CHARACTERISTICS, $V_{GS} = 10 \text{ V}$ (Note 3)							
Turn-On Delay Time	$t_{\text{d}(\text{on})}$	$V_{GS} = 10 \text{ V}, V_{DS} = 40 \text{ V}, I_D = 80 \text{ A}, R_G = 6 \Omega$	—	38	—	—	ns
Rise Time	t_r		—	34	—	—	ns
Turn-Off Delay Time	$t_{\text{d}(\text{off})}$		—	74	—	—	ns
Fall Time	t_f		—	37	—	—	ns
DRAIN-SOURCE DIODE CHARACTERISTICS							
Forward Diode Voltage	V_{SD}	$I_S = 80 \text{ A}, V_{GS} = 0 \text{ V}$	$T_J = 25^\circ\text{C}$	—	0.8	1.3	V
		$I_S = 80 \text{ A}, V_{GS} = 0 \text{ V}$	$T_J = 125^\circ\text{C}$	—	0.7	—	V
Reverse Recovery Time	t_{rr}	$I_F = 40 \text{ A}, \text{di}/\text{dt} = 300 \text{ A}/\mu\text{s}$	—	19	—	—	nS
Reverse Recovery Charge	Q_{rr}		—	42	—	—	nC
Reverse Recovery Time	t_{rr}	$I_F = 40 \text{ A}, \text{di}/\text{dt} = 1000 \text{ A}/\mu\text{s}$	—	17	—	—	nS
Reverse Recovery Charge	Q_{rr}		—	121	—	—	nC

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

3. Switching characteristics are independent of operating junction temperatures

TYPICAL CHARACTERISTICS




Figure 1. On-Region Characteristics




Figure 2. $R_{DS(on)}$ Normalized vs. I_D Figure 3. $R_{DS(on)}$ vs. Junction Temperature

Figure 4. On-Resistance vs. Gate-to-Source Voltage




Figure 5. Drain Current vs. Gate-to-Source Voltage










Figure 6. Reverse Drain Current vs. Body Diode Forward Voltage

TYPICAL CHARACTERISTICS



TYPICAL CHARACTERISTICS




Figure 13. Transient Thermal Impedance

DEVICE ORDERING INFORMATION


Device	Marking	Package	Shipping [†]
NTBLS1D5N08MC	NTBLS 1D5N08MC	M0-299A (Pb-Free)	2000 / Tape & Reel

[†]For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.



H-PSOF8L 11.68x9.80x2.30, 1.20P
CASE 100CU
ISSUE F

DATE 30 JUL 2024



*This information is generic. Please refer to device data sheet for actual part marking. Pb-Free indicator, "G" or microdot "■", may or may not be present. Some products may not follow the Generic Marking.

DOCUMENT NUMBER:	98AON13813G	Electronic versions are uncontrolled except when accessed directly from the Document Repository. Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red.
DESCRIPTION:	H-PSOF8L 11.68x9.80x2.30, 1.20P	PAGE 1 OF 1

onsemi and Onsemi are trademarks of Semiconductor Components Industries, LLC dba onsemi or its subsidiaries in the United States and/or other countries. onsemi reserves the right to make changes without further notice to any products herein. onsemi makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. onsemi does not convey any license under its patent rights nor the rights of others.

onsemi, **ONSEMI**, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "**onsemi**" or its affiliates and/or subsidiaries in the United States and/or other countries. **onsemi** owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of **onsemi**'s product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. **onsemi** reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and **onsemi** makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using **onsemi** products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by **onsemi**. "Typical" parameters which may be provided in **onsemi** data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. **onsemi** does not convey any license under any of its intellectual property rights nor the rights of others. **onsemi** products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use **onsemi** products for any such unintended or unauthorized application, Buyer shall indemnify and hold **onsemi** and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that **onsemi** was negligent regarding the design or manufacture of the part. **onsemi** is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

ADDITIONAL INFORMATION

TECHNICAL PUBLICATIONS:

Technical Library: www.onsemi.com/design/resources/technical-documentation
onsemi Website: www.onsemi.com

ONLINE SUPPORT: www.onsemi.com/support

For additional information, please contact your local Sales Representative at
www.onsemi.com/support/sales

