

ATC 100 E Series Porcelain High RF Power Multilayer Capacitors

- Case E Size (.380" x .380")
- High Q
- Low ESR/ESL
- High RF Power
- Extended WVDC up to 7200 VDC
- Capacitance Range 1 pF to 5100 pF
- Ultra-Stable Performance
- High RF Current/Voltage
- High Reliability
- Available with Encapsulation Option*

ATC, the industry leader, is announcing new improved ESR/ESL performance for the 100 E Series RF Capacitors. This high Q multilayer capacitor is ultra-stable under high RF current and voltage applications. Porcelain construction provides a rugged, hermetic package.

ATC offers an encapsulation option for applications requiring extended protection against arc-over and corona.

Typical functional applications: Bypass, Coupling, Tuning, Impedance Matching and DC Blocking.

Typical circuit applications: HF/RF Power Amplifiers, Transmitters, Antenna Tuning, Plasma Chambers and Medical (MRI coils).

*For leaded styles only

ENVIRONMENTAL TESTS

ATC 100 E Series Capacitors are designed and manufactured to meet and exceed the requirements of EIA-198, MIL-PRF-55681 and MIL-PRF-123.

THERMAL SHOCK:

MIL-STD-202, Method 107, Condition A.

MOISTURE RESISTANCE:

MIL-STD-202, Method 106.

LOW VOLTAGE HUMIDITY:

MIL-STD-202, Method 103, Condition A, with 1.5 Volts DC applied while subjected to an environment of 85°C with 85% relative humidity for 240 hours min.

LIFE TEST:

MIL-STD-202, Method 108, for 2000 hours, at 125°C. Voltage applied.

1 pF to 680 pF: at WVDC

820 pF to 2200 pF: 120% of WVDC

2700 pF to 5100 pF: 200% of WVDC



ELECTRICAL AND MECHANICAL SPECIFICATIONS

QUALITY FACTOR (Q):

Greater than 10,000 (1 pF to 1000 pF) @ 1 MHz.

Greater than 10,000 (1100 pF to 5100 pF) @ 1 KHz.

TEMPERATURE COEFFICIENT OF CAPACITANCE (TCC):

+90 ±30 PPM/°C (-55°C to +125°C)

INSULATION RESISTANCE (IR):

1 pF to 5100 pF:

10⁵ Megohms min. @ +25°C at 500 VDC.

10⁴ Megohms min. @ +125°C at 500 VDC.

WORKING VOLTAGE (WVDC):

See Capacitance Values Table, page 2.

DIELECTRIC WITHSTANDING VOLTAGE (DWV):

* See page 2.

RETRACE: Less than ±(0.02% or 0.02 pF), whichever is greater.

AGING EFFECTS: None

PIEZOELECTRIC EFFECTS: None

(No capacitance variation with voltage or pressure).

CAPACITANCE DRIFT: ±(0.02% or 0.02 pF), whichever is greater.

OPERATING TEMPERATURE RANGE:


From -55°C to +125°C (No derating of working voltage).

TERMINATION STYLES:

Available in various surface mount and leaded styles.

See Mechanical Configurations, page 3.

TERMINAL STRENGTH: Terminations for chips and pellets withstand a pull of 10 lbs. min., 25 lbs. typical, for 5 seconds in direction perpendicular to the termination surface of the capacitor. Test per MIL-STD-202, method 211.



AMERICAN TECHNICAL CERAMICS
COMPONENT AND CUSTOM INTEGRATED PACKAGING SOLUTIONS
FOR RF, MICROWAVE AND TELECOMMUNICATIONS

www.atceramics.com

ATC North America
631-622-4700
sales@atceramics.com

ATC Europe
+46 8 6800410
sales@atceramics-europe.com

ATC Asia
631-622-4700
sales@atceramics-asia.com

ATC # 001-809 Rev. F
6/02; 1 of 12

ATC 100 E Capacitance Values

CAP. CODE	CAP. (pF)	TOL.	RATED WVDC		CAP. CODE	CAP. (pF)	TOL.	RATED WVDC		CAP. CODE	CAP. (pF)	TOL.	RATED WVDC
			STD.	EXT.				STD.	EXT.				
1R0	1.0	B, C, D	3600	7200	180	18	F, G, J, K, M	3600	7200	331	330	F, G, J, K, M	3600
1R2	1.2				220	22				391	390		
1R5	1.5				270	27				471	470		2500
1R8	1.8				330	33				561	560		
2R2	2.2				390	39				681	680		1000
2R7	2.7				470	47				821	820		
3R3	3.3				560	56				102	1000		
3R9	3.9				680	68				122	1200		
4R7	4.7				820	82				152	1500		
5R6	5.6				101	100				182	1800		
6R8	6.8	121	120	222	2200								
8R2	8.2	151	150	272	2700								
100	10	F, G, J, K, M			181	180			332	3300	G, J, K, M	500	
120	12				221	220			472	4700			
150	15				271	270			512	5100			


$$VRMS = 0.707 \times WVDC$$

- SPECIAL VALUES, TOLERANCES AND MATCHING AVAILABLE. • EXTENDED WORKING VOLTAGES ARE AVAILABLE FOR COMMERCIAL ORDERS ONLY.
- ENCAPSULATION OPTION AVAILABLE. PLEASE CONSULT FACTORY.

- * DWV: 1 pF to 680 pF: 120% of rated WVDC for 5 secs.
820 pF to 2200 pF: 150% of rated WVDC for 5 secs.
2700 pF to 5100 pF: 250% of rated WVDC for 5 secs.

CAPACITANCE TOLERANCE								
Code	B	C	D	F	G	J	K	M
Tol.	±0.1 pF	±0.25 pF	±0.5 pF	±1%	±2%	±5%	±10%	±20%

ATC PART NUMBER CODE



The above part number refers to a 100 E Series (case size E) 390 pF capacitor, K tolerance (±10%), 3600 WVDC, with W termination (solder plate), laser marking and Waffle-packaging.

ATC accepts orders for our parts using designations **with** or **without** the "ATC" prefix. Both methods of defining the part number are equivalent, i.e., part numbers referenced with the "ATC" prefix are interchangeable to parts referenced without the "ATC" prefix. Customers are free to use either in specifying or procuring parts from American Technical Ceramics.

For additional information and catalogs contact your ATC representative or call direct at (631) 622-4700.

Consult factory for additional performance data.











AMERICAN TECHNICAL CERAMICS

ATC North America
631-622-4700 • sales@atceramics.com

ATC Europe
+46 8 6800410 • sales@atceramics-europe.com

ATC Asia
631-622-4700 • sales@atceramics-asia.com

ATC 100 E Capacitors: Mechanical Configurations

ATC SERIES & CASE SIZE	ATC TERM. CODE	CASE SIZE & TYPE	OUTLINES W/T IS A TERMINATION SURFACE	BODY DIMENSIONS Inches (mm)			LEAD AND TERMINATION DIMENSIONS AND MATERIALS				
				LENGTH (L)	WIDTH (W)	THICKNESS (T)	OVERLAP (Y)	MATERIALS			
100E	*W	E  Solder Plate		.380 +0.015 -.010 (9.65 +0.38 - 0.25)	.380 ±.010 (9.65 ±0.25)	.170 (4.32) max.	.040 (1.02) max.	SOLDER PLATE Nickel barrier, solder plated. Rugged, high performance termination for lower cost, high volume applications			
100E	P	E  Pellet		.380 +0.080 -.010 (9.65 +2.03 - 0.25)				BARRIER /CAP® Nickel barrier, solder plated with the addition of hot solder dip process. Solder melting temperature is 355°F, 179°C.			
100E	CA	E  Gold Chip		.380 +0.015 -.010 (9.65 +0.38 - 0.25)				UNI-TERM® NICKEL BARRIER, GOLD PLATED TERMINATIONS			
100E	MS	E  Microstrip		.380 +0.035 -.010 (9.65 +0.89 - 0.25)				High Purity Silver Leads L _L = .750 (19.05) min. W _L = .350 ±0.010 (8.89 ±0.25) T _L = .010 ±0.005 (0.25 ±0.13) Leads are Attached with High Temperature Solder.			
100E	AR	E  Axial Ribbon						Silver-plated Copper Leads Dia. = .032 ±.002 (.813 ±.051) L _L = 2.25 (57.2) min.			
100E	AW	E  Axial Wire						Silver-plated Copper Leads Dia. = .032 ±.002 (.813 ±.051) L _L = 1.0 (25.4) min.			
100E	RW	E  Radial Wire									

Custom lead styles and lengths are available; consult factory.

All 100 E Capacitors are available laser marked with ATC's identification, capacitance code and tolerance.

* Replaces C Termination

A M E R I C A N T E C H N I C A L C E R A M I C S

ATC North America
631-622-4700 • sales@atceramics.com


ATC Europe
+46 8 6800410 • sales@atceramics-europe.com

ATC Asia
631-622-4700 • sales@atceramics-asia.com

w w w . a t c e r a m i c s . c o m

ATC # 001-809 Rev. F 6/02; 3 of 12

ATC 100 E Capacitors: Non-Magnetic Mechanical Configurations

ATC SERIES & CASE SIZE	ATC TERM. CODE	CASE SIZE & TYPE	OUTLINES W/T IS A TERMINATION SURFACE	BODY DIMENSIONS Inches (mm)			LEAD AND TERMINATION DIMENSIONS AND MATERIALS	
				LENGTH (L)	WIDTH (W)	THICKNESS (T)	OVERLAP (Y)	MATERIALS
100E	*WN	E  Non-Mag Solder Plate		.380 +.015 -.010 (9.65 +0.38 - 0.25)	 <			

Custom lead styles and lengths are available; consult factory.

All 100 E Capacitors are available laser marked with ATC's identification, capacitance code and tolerance.

* Replaces CN Termination

A M E R I C A N T E C H N I C A L C E R A M I C S


ATC North America
631-622-4700 • sales@atceramics.com

ATC Europe
+46 8 6800410 • sales@atceramics-europe.com


ATC Asia
631-622-4700 • sales@atceramics-asia.com

ATC 100 E Performance Data

ESR VS CAPACITANCE ATC SERIES 100, CASE E



Q VS CAPACITANCE ATC SERIES 100, CASE E



A M E R I C A N T E C H N I C A L C E R A M I C S

ATC North America
631-622-4700 • sales@atceramics.com

ATC Europe
+46 8 6800410 • sales@atceramics-europe.com


ATC Asia
631-622-4700 • sales@atceramics-asia.com

www.atceramics.com


ATC # 001-809 Rev. F 6/02; 5 of 12

ATC 100 E Performance Data

ESR VS CAPACITANCE ATC SERIES 100, CASE E



Q VS CAPACITANCE ATC SERIES 100, CASE E



A M E R I C A N T E C H N I C A L C E R A M I C S


ATC North America
631-622-4700 • sales@atceramics.com

ATC Europe
+46 8 6800410 • sales@atceramics-europe.com


ATC Asia
631-622-4700 • sales@atceramics-asia.com

ATC 100 E Performance Data

SERIES RESONANCE VS CAPACITANCE
ATC SERIES 100, CASE E



CAPACITANCE CHANGE VS TEMPERATURE
ATC SERIES 100, CASE E



A M E R I C A N T E C H N I C A L C E R A M I C S

ATC North America
631-622-4700 • sales@atceramics.com

ATC Europe
+46 8 6800410 • sales@atceramics-europe.com


ATC Asia
631-622-4700 • sales@atceramics-asia.com

w w w . a t c e r a m i c s . c o m


ATC # 001-809 Rev. F 6/02; 7 of 12

ATC 100 E Performance Data

CURRENT RATING VS CAPACITANCE ATC SERIES 100, CASE E



CURRENT RATING VS CAPACITANCE ATC SERIES 100, CASE E



A M E R I C A N T E C H N I C A L C E R A M I C S


ATC North America
631-622-4700 • sales@atceramics.com

ATC Europe
+46 8 6800410 • sales@atceramics-europe.com

ATC Asia
631-622-4700 • sales@atceramics-asia.com

ATC 100 E Performance Data

CURRENT RATING VS CAPACITANCE ATC SERIES 100, CASE E, EXTENDED VOLTAGE



A M E R I C A N T E C H N I C A L C E R A M I C S

ATC North America
631-622-4700 • sales@atceramics.com

ATC Europe
+46 8 6800410 • sales@atceramics-europe.com

ATC Asia
631-622-4700 • sales@atceramics-asia.com

w w w . a t c e r a m i c s . c o m

ATC # 001-809 Rev. F 6/02; 9 of 12

Notes

A M E R I C A N T E C H N I C A L C E R A M I C S

ATC North America **ATC Europe** **ATC Asia**
631-622-4700 • sales@atceramics.com +46 8 6800410 • sales@atceramics-europe.com 631-622-4700 • sales@atceramics-asia.com

Notes

A M E R I C A N T E C H N I C A L C E R A M I C S


ATC North America
631-622-4700 • sales@atceramics.com

ATC Europe
+46 8 6800410 • sales@atceramics-europe.com

ATC Asia
631-622-4700 • sales@atceramics-asia.com

w w w . a t c e r a m i c s . c o m

ATC # 001-809 Rev. F 6/02; 11of 12



www.atceramics.com

AMERICAN TECHNICAL CERAMICS
COMPONENT AND CUSTOM INTEGRATED PACKAGING SOLUTIONS
FOR RF, MICROWAVE AND TELECOMMUNICATIONS

ATC North America
631-622-4700
sales@atceramics.com

ATC Europe
+46 8 6800410
sales@atceramics-europe.com

ATC Asia
631-622-4700
sales@atceramics-asia.com

ATC has made every effort to have this information as accurate as possible. However, no responsibility is assumed by ATC for its use, nor for any infringements of rights of third parties which may result from its use. ATC reserves the right to revise the content or modify its product line without prior notice.

© 1996 American Technical Ceramics Corp.

ATC # 001-809 Rev. F 6/02; 12 of 12