REVISIONS					
REV	ECO	DESCRIPTION	DATE	BY	APPR
A1	--	RELEASED DRAWING	MAR-18-16	JARRY	TOMMY





NOTES : (UNLESS OTHERWISE SPECIFIED)

1. MATERIAL :
   SHELL : THERMOPLASTIC , UL94 V-0.
   SEAL GASKET : NBR OR SR.
2. SPECIFICATIONS :
   2.1 OPERATING TEMPERATURE : SEE TABLE.
   2.2 INSULATION RESISTANCE : 5000 MEGOHMS MIN.
   2.3 IP CLASS : IP67.
   2.4 MATING CYCLES DURABILITY : 500 CYCLES MIN.
   2.5 RoHS COMPLIANT.
3. ALL DIMENSIONS ARE FOR REFERENCE USE ONLY.

KEY	PART NUMBER	
	-40°C ~ 105°C	-40°C ~ 125°C
N	RTS614*DCG	RTS614*DCG03

QUANTITY	PART NUMBER	DESCRIPTION	ITEM

MATERIALS LIST

UNLESS OTHERWISE SPECIFIED
1) All dimensions are in metric(mm).
2) Tolerances are as follows:
1 PL DEC ±0.30 | Fractions ±1/64
2 PL DEC ±0.15 | Angles ±1°
3 PL DEC ±0.08
3) Note reference = X

MATERIAL SPECIFICATIONS:

PROCESS SPECIFICATIONS:

NEXT ASS'Y:

SIGNATURES		DATE
DRAWN:	JARRY	MAR-18-16
CHECKED:		
ENGINEER:		
APPROVAL:		
CUSTOMER:		

THIS DRAWING IS SUPPLIED FOR INFORMATION ONLY. DESIGN FEATURES, SPECIFICATIONS AND PERFORMANCE DATA SHOWN HEREON ARE THE PROPERTY OF THE AMPHENOL CORPORATION. NO RIGHTS OF REPRODUCTION ARE IMPLIED. ALL DIMENSIONS ARE SUBJECT TO NORMAL MANUFACTURING VARIATIONS.

Amphenol
Sine Systems - www.amphenol-sine.com
44724 Morley Drive
Clinton Township, MI 48036

ECO-MATE,PLUG SEALING CAP,SIZE 14

SIZE	TYPE	DWG NO:	REVISION
B	C-	RTS614*DCG*	A1

SCALE: NONE SHEET 1 OF 1

TITLE: ECO-MATE,PLUG SEALING CAP,SIZE 14
DWG NO: RTS614*DCG*
REV: A1
SH: 1
OF: 1

Downloaded from Arrow.com.