

Dimension L&B

DIM L	N×5.0
DIM B	(N-1)×5.0

N=Number of poles

Poles	L&B Tolerance
4P-8P	±0.15
9P-14P	±0.25
15P-20P	±0.35
21P-24P	±0.40



SIGN	DATE	DESCRIPTION	APPROVER
△	2/10`06	Part NO is Changed	xionghaitao
△	01/12`07	Soldering temperature changed from 245° to 250°	Tason
△	12/06`13	Update the drawing	Guoxue

THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!

Material

- Item ㉑ Clamp : Brass , Ni plated
- Item ㉒ Terminal screw: Steel , Zinc plating "- slot type
- Item ㉓ Wire guard solder pin : Brass , Tin plated
- Item ㉔ Terminal housing : Thermoplastic (UL94V-0)

Electrical UL



- Voltage rating: 300VAC
- Current rating: 10A
- Wire range:
- Solid wire(AWG): 12-24
- Stranded wire(AWG): 12-24
- Torque(Lb-In): 3.5
- Screw: M2.5
- Wire strip length: 6-7mm
- Withstanding Voltage: 1.6KV
- Operating temperature: -40°C to +115°C
- Soldering temperature: 260°C±5°C/5 Sec
- Safety Approval Deta: 
- Critical dimension: 

△△ T2 xx 0 1 x 1 xxxx G

04 4 POLES
05 5 POLES
...
24 24 POLES

Color
0 Black (RAL9005)
2 Red (RAL3001/D)
3 Orange(RAL2011/P)
4 Yellow(RAL1018/A)
5 Green(RAL6018/T)
6 Blue (RAL5015/A)
8 Grey(RAL7035/D)
C Green(RAL6018/U)


0000:"@Logo (Standard) RoHS compliant
000A:"ANYTEK"Logo (lead<4%)
0091:"ANYTEK"Logo In copper Alloy
Any special item by
customer request,
please contact sales
department.



ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE		T2 - 5.0mm series 4P-24P (Solid Block)			
PART NO.	T2xx01x1xxxxG			DWG NO.	8T20101
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.	
		Guoxue 2013.12.06	Guoxue 2013.12.06		Tolerance
				UNIT: mm	X. ±0.50
				SCALE: NONE	X.X ±0.30
					X.XX ±0.10
					X° ±1°

SHEET: 01/01

REV.: E