




1		2
---	--	---



MATERIALS ELECTRICAL
RATED VOLTAGE & CURRENT:
WITHSTAND VOLTAGE:
INSULATION RESISTANCE:
OPERATING TEMPERATURE RANGE:
SCREW TORQUE VALUE:
WIRE RANGE:
1) HOUSING:
2) TERMINAL:
3) TERMINAL SCREWS:

300 V, 15 A
AC 2000 V/Min
1000 M Ω OR MORE AT DC 500 V
-40 °C ~ +115 °C
5.2 Lb-In.
14 ~ 22 AWG
THERMOPLASTIC, UL 94 V-0 BLACK
BRASS, 0.8t
STEEL, M3

Dim A	$(N-1) \times 7.62 + 9.54$
Dim B	$(N-1) \times 7.62$

Poles	Tolerance
2p-4p	± 0.20
5p-10p	± 0.30
11p-16p	± 0.40
17p-18p	± 0.50

No. of poles
02 2 poles
03 3 poles
...
18 18 poles

Code	Terminal	Screw
0	G/F	G/F
1	G/F	Zinc
2	Tin	G/F
3	Tin	Zinc

RoHS compliant
(lead<4%)
In copper Alloy

[illegible]