








PRINTED CIRCUIT BOARD
LAND DIMENSIONS



CIRCUIT DIAGRAM




Compliance: RohS II (2011/65/EU)

Tolerances: up to 10: ±0.2mm above 10-50: ±0.3mm			Date	Name	TSS 66 x-T			
			06/15	dr				
			knitter-switch			30 33 64		Page
Material	05/18	dr						
Packaging unit	07/15	dr						1/3
Modifications	Date	Name						

Specifications:

Contact rating: 50mA, 12V DC
Contact resistance: 100mOhm max.
Insulation resistance: 100MOhm min. at 500V DC for 1 minute
Dielectric strength: 250V AC (50/60Hz) for 1 minute
Operating temperature: -40°C to +85°C
Storage temperature: -40°C to +85°C
Material: Cover: stainless steel
Case / stem: PPS
Contact: phosphor bronze, silver plated
Terminal: brass, silver plated

Soldering conditions:




x	Operating force	Mechanical life	Stem color
K	100 +/-30 gf	150 000 cycles	black
N	160 +/-50 gf	150 000 cycles	brown
R	250 +/-70 gf	150 000 cycles	red
S	320 +/-70 gf	100 000 cycles	salmon
Y	520 +/-130 gf	50 000 cycles	yellow

Compliance: RohS II (2011/65/EU)

Tolerances: up to 10: ±0.2mm above 10-50: ±0.3mm			Date	Name	TSS 66 x-T		
			06/15	dr			
			knitter-switch		30 33 64		Page
Material	05/18	dr					2/3
Packaging unit	07/15	dr					
Modifications	Date	Name					

Packaging:



Packaging unit: 300 pcs. / reel
Compliance: RohS II (2011/65/EU)

Tolerances: up to 10: ±0.2mm above 10-50: ±0.3mm			Date	Name	TSS 66 x-T		
			06/15	dr			
Material	05/18	dr	knitter-switch			30 33 64	Page
Packaging unit	07/15	dr					3/3
Modifications	Date	Name					