





LOC	DIST	REVISIONS					
-	-	P	LTR	DESCRIPTION	DATE	DWN	APVD
		B		REV PER ECO 12-010940	7-31-12	CT	DH
		C		ECO-13-004755	26MAR2013	KG	DH
		D		ECO-14-017030	25NOV2014	MGM	CT




$\oplus \varnothing 0.05 \textcircled{S} X Y$

FINISHED HOLE SIZE
AND PLATED THRU HOLES



- 1 MATERIAL:
CONTACT - COPPER ALLOY
HOUSING - LCP, COLOR - BLACK
- 2 FINISH:
MATING AREA: 1.27 μ m MIN GOLD OVER
1.27 μ m MIN NICKEL
- 3 FINISH:
COMPLIANT PIN AREA: 0.38 μ m MIN BRIGHT TIN LEAD
OVER 1.27 μ m MIN NICKEL
- 4 FINISH:
COMPLIANT PIN AREA: 0.38 μ m MIN MATTE TIN
OVER 1.27 μ m MIN NICKEL
- 5 ---
- 6 DATUMS AND BASIC DIMENSIONS ESTABLISHED BY CUSTOMER.
- 7 REFERENCE APPLICATION SPEC 114-13267 FOR RECOMMENDED
PLATING THRU HOLE DIAMETER AND PLATING THICKNESS.

$\triangle 2$ $\triangle 4$	2102157-2
$\triangle 2$ $\triangle 3$	2102157-1
FINISH	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT. DIMENSIONING AND TOLERANCING PER GPS (150 STANDARDS)		DWN D. BELACK 24JUN2009	 TE Connectivity	
		CHK A. TSANG 6-24-2009		
DIMENSIONS:		APVD W. McALONIS 6-24-2009	NAME Fortis Zd. 3-PAIR, 10-COLUMN, VERTICAL, SINGLE MODULE ASSEMBLY	
mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	PRODUCT SPEC 108-2409	-	
	0 PLC ±.13 1 PLC ±0.13 2 PLC ±.05 3 PLC ±. 4 PLC ±. ANGLES ±2°	APPLICATION SPEC 114-13267	SIZE A1	CAGE CODE 00779
MATERIAL	FINISH	WEIGHT ~3.83g	DRAWING NO C=2102157	RESTRICTED TO -
	-	CUSTOMER DRAWING	SCALE 8:1	SHEET 1 OF 1
			REV D	