

VLS3010ET-100M

Production (NRND)

Product Status Recommended Alternate Part No. : [VLS3012CX-100M-1](#) (Interchangeability is not guaranteed.)

Applications Commercial Grade

Wire Wound Wire Wound

Feature Shield Magnetic Shield
Ferrite Core Ferrite Core

Series | Type VLS-E

Brand TDK

Environmental Compliance  RoHS  REACH  Halogen Free  Lead Free



Size

Length(L)	3.00mm $\pm 0.10\text{mm}$
Width(W)	3.00mm $\pm 0.10\text{mm}$
Thickness Height	1.00mm Max.
Recommended Land Pattern (A)	1.00mm Nom.
Recommended Land Pattern (B)	1.00mm Nom.
Recommended Land Pattern (C)	3.00mm Nom.

Electrical Characteristics

Inductance	10 μH $\pm 20\%$ at 1MHz
Rated Current (L Change) [Typ.]	630mA (30% Down)
Rated Current (L Change) [Max.]	560mA (30% Down)
Rated Current (Temperature Rise) [Typ.]	800mA (40°C Rise)
Rated Current (Temperature Rise) [Max.]	
DC Resistance [Typ.]	390m Ω
DC Resistance [Max.]	468m Ω
Rated Voltage [Max.]	
Self Resonant Frequency [Min.]	
Self Resonant Frequency [Typ.]	
Q [Min.]	
Q [Typ.]	

Other

Operating Temp. Range	-40 to 105°C (Including Self-Temp. Rise)
Soldering Method	Reflow
AEC-Q200	NO
Packing	Embossed (Plastic)Taping [180mm Reel]

! Images are for reference only and show exemplary products.

! This PDF document was created based on the data listed on the TDK Corporation website.

! All specifications are subject to change without notice.







VLS3010ET-100M

Package Quantity	2000pcs
Weight	0.036g

! Images are for reference only and show exemplary products.
! This PDF document was created based on the data listed on the TDK Corporation website.
! All specifications are subject to change without notice.

VLS3010ET-100M

Characteristic Graphs (This is reference data, and does not guarantee the products characteristics.)




! Images are for reference only and show exemplary products.

! This PDF document was created based on the data listed on the TDK Corporation website.

! All specifications are subject to change without notice.

VLS3010ET-100M



Characteristic Graphs (This is reference data, and does not guarantee the products characteristics.)



! Images are for reference only and show exemplary products.
! This PDF document was created based on the data listed on the TDK Corporation website.
! All specifications are subject to change without notice.

VLS3010ET-100M

Associated Images



! Images are for reference only and show exemplary products.
! This PDF document was created based on the data listed on the TDK Corporation website.
! All specifications are subject to change without notice.