

NOTES:

1. MATERIALS AND FINISHES:

BODY - BRASS, ALBALOY PLATING

CONTACT - BRASS, GOLD PLATING

INSULATOR - PTFE

2. ELECTRICAL:

A. IMPEDANCE: 50 OHM

B. FREQUENCY RANGE: DC 0 - 11 GHz

C. DIELECTRIC WITHSTANDING VOLTAGE: 2500 VRMS, MIN.

3. MECHANICAL:

A. DURABILITY: 500 CYCLES MIN.

B. TEMPERATURE RANGE: -65° C TO +165° C


3. PACKAGING:

A. PACK ONE CONNECTOR IN A BAG AND MARK ON THE BAG: "6600-1313 82-6304"

B. PACK TWENTY-FIVE WRAPPED CONNECTORS IN A MASTER BAG AND MARK ON THE MASTER BAG: "LORCH P/N: 6600-1313 P/N: 82-6304"

C. O-RING MAY BE PACKAGED LOOSE.



THIRD ANGLE PROJ.



SCALE 2.000

REVISIONS

REV	DESCRIPTION	DATE	ECO	APPR
AI	SEE SHEET 1	09-Jul-07	--	--
E	UPDATE THE DRAWING	08-Jul-09	47563	SH
F	INSULATOR WAS CHANGED \RD-DM14072301R3	31-Jul-14	50117	RM



CUSTOMER OUTLINE DRAWING

ALL OTHER SHEETS ARE FOR INTERNAL USE ONLY

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN METRIC AND TOLERANCES ARE: <0.5mm 0.5 - 6mm 6 - 30mm 30 - 120mm ANGLES ± 0.05mm ±0.1mm ±0.2mm ± 0.3mm ±1° NOTICE - These drawings, specifications, or other data (1) are, and remain the property of Amphenol corp. (2) must be returned upon request; and (3) are confidential and not to be disclosed to any person other than those to whom they are given by Amphenol Corp. the furnishing of these drawings, specifications, or other data by Amphenol Corp., or to any other person to anyone for any purpose is not to be regarded by implicatioin or otherwise in any manner licensing, granting rights to permitting such holder or any other sperson to manufacture, use or sell any product, process or design, patented or otherwsie, that may in any way be related to or disclosed by said drawings, specifications, or other data.	MATERIAL - REFERENCE EAR # 644 AND CONFIGURATION LEVEL: ☐☐☐ FINISH	DRAWN R. MAO	DATE 31-Jul-14	TITLE N PANEL RECEPT. PLUG		Amphenol RF Danbury CT USA, Tainan, Taiwan, Shenzhen, China www.amphenolrf.com	
		ENGINEER C. WANG	DATE 14-Aug-08				
		APPROVED S. HSIEH	DATE 31-Jul-14	SCALE: 3.0:1.0		SHEET 2 OF 2	
		CAD FILE		DWG SIZE		REV	
				B		F	
						DRAWING NO. NI55IEI-004-AT50GA-50	
						ITEM NO. 031551AAQ02AL5F	
						PART NO. 82-6304	