Part Number : 732830321
Product Description : High-Density EMI Filtered D-Sub Adapter, Male-to-Female, Straight, 4000pF C, 15 Circuits
Series Number : 73283
Status : Active
Product Category : D-Sub Connectors



Documents and Resources

Drawings

732830321_sd.pdf

STEP AP242

SOLIDWORKS

Creo

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Reviewed per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Not Reviewed per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Downloaded from Arrow.com.

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	D-Sub Connectors
Series	73283
Description	High-Density EMI Filtered D-Sub Adapter, Male-to-Female, Straight, 4000pF C, 15 Circuits
Application	RF
Component Type	Adapter
Product Name	EMI Filtered D-Sub
Type	High Density EMI Filtered
UPC	198282750932

Electrical

Current - Maximum per Contact	3.0A
Capacitance Value	4000 pF
Capacitance Tolerance	± 25%
3 dB Cut-off Frequency Max. (MHz)	1.3
Dielectric Withstanding Voltage (V)	300
EMI Filter Circuits	Capacitive
Minimum Insertion Loss (dB) - 1 GHz	48
Minimum Insertion Loss (dB) - 10 MHz	13
Minimum Insertion Loss (dB) - 100 MHz	31
Minimum Insertion Loss (dB) - 20 MHz	19
Minimum Insertion Loss (dB) -	37

Downloaded from Arrow.com.

200 MHz	
Minimum Insertion Loss (dB) - 5 MHz	8
Minimum Insertion Loss (dB) - 50 MHz	26
Minimum Insertion Loss (dB) - 500 MHz	45
Voltage - Maximum	100V DC

Physical

Circuits (Loaded)	15
Circuits (maximum)	15
Color - Resin	Blue
Durability (mating cycles max)	500
Gender	Male/Female
Material - Contact	Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Gold
Material - Resin	Polyester
Material - Shell	Zinc
Number of Rows	3
Orientation	Straight
Packaging Type	Tray
Panel Mount	Rear
Panel Mount Method	Hardware
PCB Locator	No
PCB Retention	No
PC Tail Length	N/A
Pitch - Mating Interface	2.29mm
Pitch - Termination Interface	2.29mm
Plating min - Mating	1.270µm
Plating min - Termination	Flash
Plating - Shell	Nickel
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Ports	1

Downloaded from Arrow.com.

Temperature Range - Operating	-55° to +125°C
Termination Style	N/A
Waterproof / Dustproof	No
Wire Size (AWG)	N/A

Downloaded from Arrow.com.