



Part Number : [1200878239](#)

Product Description : Nano-Change (M8) Double-Ended Cordset with Knurled Hexnut, 5 Poles, B-Coded, Male (Straight) to Female (Straight), 24 AWG, Black PVC Cable, 0.60m (1.97') Length

Series Number : 120087

Status : Active

Product Category : Circular Industrial Cordsets

Engineering Part Number : 445030E02M006




Documents and Resources

Drawings

[1200878239_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration

- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

UKCA - Declaration of Conformity

CE - Declaration of Conformity

Part Details

General

Status	Active
Category	Circular Industrial Cordsets
Series	120087
Description	Nano-Change (M8) Double-Ended Cordset with Knurled Hexnut, 5 Poles, B-Coded, Male (Straight) to Female (Straight), 24 AWG, Black PVC Cable, 0.60m (1.97') Length
IP Rating	IP67
Product Name	Nano-Change (M8)
Type	Double Ended
UPC	78172511673

Electrical

Current - Maximum per Contact	3.0A
Voltage - Maximum	30V AC/DC

Physical

Cable Diameter	5.30mm (.209")
Cable Length	0.60m (1.97')
Color - Cable Jacket	Black
Connector End A	Nano-Change (M8)
Connector End B	Nano-Change (M8)
Coupling Style	Threaded
Gender	Female-Male

Keyway	B-Coded
LED Indicator	None
Material - Cable Jacket	PVC
Material - Connector Body	TPU
Material - Contact	Brass
Material - Coupling Nut	Nickel-plated Brass
Material - O-Ring	Fluoro-elastomer
Material - Plating Mating	Gold
Net Weight	32.221/g
Orientation	Straight to Straight
Poles	5
Temperature Range - Operating	-25° to +80°C
Wire/Cable Type	UL 2464
Wire Size (AWG)	24

This document was generated on Jun 06, 2026