



Part Number : [420241017](#)
Product Description : MLX Female Crimp Terminal,
20-18 AWG, Brass, Tin (Sn) Plating, Reel
Series Number : 42024
Status : Active
Product Category : Crimp Terminals



Documents and Resources

Drawings

[420241017_sd.pdf](#)

Specifications

[PS-42022-0001-001.pdf](#)

[TS-42022-0001-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Crimp Terminals
Series	42024
Description	MLX Female Crimp Terminal, 20-18 AWG, Brass, Tin (Sn) Plating, Reel
Application	Power, Wire-to-Board, Wire-to-Wire
Product Name	MLX
UPC	887191525211

Physical

Gender	Female
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.691/g
Packaging Type	Reel
Plating min - Mating	0.508µm
Plating min - Termination	0.508µm
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	1.65-2.95mm
Wire Size (AWG)	18, 20
Wire Size mm ²	N/A

This document was generated on Apr 30, 2026