



Technical Data

05.09.2022

Heat Shrinkable Tubing 2:1 flexible and transparent
HFT-B - halogen free

HFT-B-9.5/4.8

Article Number 305-09519



Material:

Polyolefin, cross-linked (PO-X)

Colour:

Transparent (CL)

Supplied Ø D min.:

9.5 mm

Recov. Ø d max.:

4.8 mm

Wall (WT):

0.60 mm

Shrink Ratio:

2:1

Longitudinal Change After Shrinkage:

-5% max.

Min. Shrink Temperature - °C:

+135 °C

Operating Temperature - °C:

-55 °C to +135 °C

Heat Shock Test:

4h/200°C

Tensile Strength at Heat Shock:

25 MPa

Elongation at Heat Shock:

540 %

Dielectric Strength:

25 kV/mm

Insulation Class:

B (VDE 0530)

Tensile Strength:

25 MPa

Elongation at break:

540%

Specifications:

DEF STAN 59-97/3, MIL-DTL-23053/5C,
NF F 00-608, SAE - AMS - DTL-23053/5C



We assume no responsibility that the Product will be used for the intended purpose, this is beyond our control. It's up to the customer to check the suitability for a specific application by means of tests. Technical changes and errors reserved