Ratings
Voltage: 600 V
Temperature: -40~105 °C
Flammability: FT2

Conductor
Conductor count: 8
Gauge: 32 AWG 0.04 mm²
Material: tinned copper strands
Strand size: ∅0.08 x 7
Resistance at 20 °C: 588 Ω /km max

Insulator
Material: mPPE
Color: red, black, white, yellow, blue, green, orange, purple
Diameter: ∅0.75 ±0.08 mm
Average thickness: 0.24 mm
Resistance at 20 °C: 100 MΩ /km min


Filler
Material: cotton rope


Wrap
Material: cotton paper

Outer jacket
Material: mPPE, 85A
Color: black
Diameter: ∅4 ±0.20 mm
Average thickness: 0.71 mm

Wire marking: E339579 UL AWM STYLE 21509 32 AWG 105°C 600V - - - cUL AWM I A 105°C 600V FT2 TENSILITY

Bend radius
Minimum: 6 times diameter (24.0 mm)





Revision:	Date:	Description:
A	5/4/2021	Initial release

Prepared: AW
Digitally signed by AW
Date: 2021.05.06 13:04:07 -07'00'

Verified: JC
Digitally signed by JC
Date: 2021.05.11 15:10:50 -07'00'

Dimensions are in millimeters.
Tolerances:
X: ± 0.5 mm
X.X: ± 0.3 mm
X.XX: ± 0.05 mm

Notes:
RoHS compliant

Phthalate and halogen free

Description:
Wire, 8C TS, 32 AWG, 21509, 600V, 105C, 4.0 mm, FT2, mPPE

TENSILITY
tel 1.541.323.3228 800 877.670.7118
fax 1.541.323.4202 web tensility.com

Size: A
Part number: 30-02029
Scale: 15:1
Sheet 1 of 1

To see a custom version of this cable assembly, call Tensility at 541-323-3228 or email engineering@tensility.com

5 4 3 2 1

Downloaded from Arrow.com.