


**Part Number :** [348621106](#)

**Product Description :** HSAutoLink II Unsealed Header, Vertical, 12 Circuits, Key A, Black

**Series Number :** 34862

**Status :** Not Recommended For New Design

**Product Category :** PCB Headers and Receptacles



---

## Documents and Resources

### Drawings

[PK-34862-001-001.pdf](#)


### Specifications

[PS-34861-001-001.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Compliant with Exemption 44; 34; 33
China RoHS	 per SJ/T 11365-2006
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

## Substances of Interest

- PFAS

## EU RoHS Certificate of Compliance

## Additional Product Compliance Information

---

### Part Details

#### General

Status	Not Recommended For New Design
Category	PCB Headers and Receptacles
Series	34862
Description	HSAutoLink II Unsealed Header, Vertical, 12 Circuits, Key A, Black
Application	Signal, Wire-to-Board
Comments	Higher current capability depending of the connector loading, please contact Molex for further technical details.
Component Type	PCB Header
Product Name	HSAutoLink II
UPC	887191705187

#### Electrical

Current - Maximum per Contact	1.5A
Voltage - Maximum	36V

#### Physical

Breakaway	No
Circuits (Loaded)	12
Circuits (maximum)	12
Color - Resin	Black
Durability (mating cycles max)	25
First Mate / Last Break	No
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	Yes

Lock to Mating Part	Yes
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	3.632/g
Number of Rows	2
Orientation	Vertical
Packaging Type	Embossed Tape on Reel
PCB Retention	Yes
PCB Thickness - Recommended	1.60mm
Pitch - Mating Interface	1.27mm
Pitch - Termination Interface	1.27mm
Plating min - Mating	0.406µm
Plating min - Termination	2.500µm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Stackable	No
Temperature Range - Operating	-40° to +105°C
Termination Interface Style	Through Hole

---

This document was generated on Apr 12, 2026