

Vectron International**Filter specification****TFS1575Z****1/5****Measurement condition**

Ambient temperature T_A :	23	°C
Input power level:	0	dBm
Terminating impedance:		
Input:	50	Ω
Output:	50	Ω

Characteristics

Remark:

The maximum attenuation in the pass band is defined as the insertion loss a_e . The nominal frequency f_N is fixed at 1575.42 MHz without any tolerance or limit. The values of absolute attenuation a_{abs} are guaranteed over the whole operating temperature range. The frequency shift of the filter within the operating temperature range is included in the production tolerance scheme.

D a t a		typ. value		tolerance / limit		
Insertion loss within PB1		a_{e1}	2.5 dB	max.	4.0	dB
Insertion loss within PB2		a_{e2}	1.8 dB	max.	2.0	dB
Nominal frequency		f_N	-		1575.42	MHz
Passband 1		PB1	-	$f_N \pm$	17.5	MHz
Passband 2		PB2	-	$f_N \pm$	10.0	MHz
Passband variation within PB1		PBV1	0.7 dB	max.	1.0	dB
Absolute attenuation		a_{abs}				
0.3 MHz ... 1425.0 MHz			43 dB	min.	32	dB
1425.0 MHz ... 1495.0 MHz			44 dB	min.	42	dB
	1540.0 MHz		14 dB	min.	10	dB *)
	1610.0 MHz		19 dB	min.	10	dB **)
1655.0 MHz ... 1725.0 MHz			52 dB	min.	42	dB
1725.0 MHz ... 3000.0 MHz			36 dB	min.	32	dB
Group delay ripple within PB1		GDR1	29 ns	max.	50	ns
Group delay ripple within PB2		GDR2	13 ns	max.	30	ns
VSWR within PB			1.8 : 1	max.	2.2 : 1	
Input power level in PB			-	max.	15	dBm
Operating temperature range		OTR	-		-45 °C ... +85 °C	
Storage temperature range			-		-55 °C ... +125 °C	
Temperature coefficient of frequency		$TC_f^{***})$	-42 ppm/K			

*) stop band attenuation between 1495.0 MHz and 1540.0 MHz decreases linearly from 42 dB to 10 dB

**) stop band attenuation between 1610.0 MHz and 1655.0 MHz increases linearly from 10 dB to 42 dB



***) $\Delta f = TC_f(T - T_A)f_N$

Generated:**Checked / Approved:**

Vectron International GmbH
Potsdamer Straße 18
D 14 513 TELTOW / Germany
Tel: (+49) 3328 4784-0 / Fax: (+49) 3328 4784-30
E-Mail: tft@vectron.com


Vectron International GmbH reserves the right to make changes to the product(s) and/or information contained herein without notice. No liability is assumed as a result of their use or application. No rights under any patent accompany the sale of any such product(s) or information.

Filter characteristic



Construction and pin connection


(All dimensions in mm)



1	Ground
2	Input
3	Ground
4	Ground
5	Output
6	Ground

Date code:	Year + week
K	2018
L	2019
M	2020
...	

50 Ω Test circuit



Vectron International GmbH
 Potsdamer Straße 18
 D 14 513 TELTOW / Germany
 Tel: (+49) 3328 4784-0 / Fax: (+49) 3328 4784-30
 E-Mail: tft@vectron.com

Vectron International GmbH reserves the right to make changes to the product(s) and/or information contained herein without notice. No liability is assumed as a result of their use or application. No rights under any patent accompany the sale of any such product(s) or information.

Stability characteristics. reliability

After the following tests the filter shall meet the whole specification:

1. Shock: 500 g, 1 ms, half sine wave, 3 shocks each plane;
DIN IEC 60068 T2 - 27
2. Vibration: 10 Hz to 2000 Hz, 0.35 mm or 5 g respectively, 1 octave per min. 10 cycles per plane, 3 planes; DIN IEC 60068 T2 - 6
3. Change of temperature: -55 °C to 125 °C / 15 min. each / 100 cycles
DIN IEC 60068 part 2 – 14 Test N
4. Resistance to solder heat (reflow): reflow possible: three times max.;
for temperature conditions refer to the attached "Air reflow temperature conditions" on page 4;
5. SAW devices are Electrostatic Discharge (ESD) sensitive devices.

This filter is RoHS compliant (2011/65/EU)

Packing

Tape & Reel: IEC 286 – 3, with exception of value for N and minimum bending radius;
tape type II, embossed carrier tape with top cover tape on the upper side;


reel of empty components at start: min. 300 mm
reel of empty components at start including leader: min. 500 mm
trailer: min. 300 mm

Tape (all dimensions in mm)

W	:8.00	±0.3
Po	:4.00	±0.1
Do	:1.50	+0.1/-0
E	:1.75	±0.1
F	:3.50	±0.05
G(min)	:0.75	
P2	:2.00	±0.05
P1	:4.00	±0.1
D1(min)	:1.50	
Ao	:3.25	±0.1
Bo	:3.25	±0.1
Ct	:5.30	±0.1
Ko	:1.50	±0.1
t	:0.25	±0.05

Reel (all dimensions in mm)

A	:330	or 180
W1	:8.40	+1.5/-0
W2(max)	:14.40	
N(min)	:60.00	
C	:13.0	±0.2




The minimum bending radius is 45 mm.

Vectron International GmbH
Potsdamer Straße 18
D 14 513 TELTOW / Germany
Tel: (+49) 3328 4784-0 / Fax: (+49) 3328 4784-30
E-Mail: tft@vectron.com

Vectron International GmbH reserves the right to make changes to the product(s) and/or information contained herein without notice. No liability is assumed as a result of their use or application. No rights under any patent accompany the sale of any such product(s) or information.

Air reflow temperature conditions

Conditions	Exposure
Average ramp-up rate (30 °C to 217 °C)	less than 3 °C / second
> 100 °C	between 300 and 600 seconds
> 150 °C	between 240 and 500 seconds
> 217 °C	between 30 and 150 seconds
Peak temperature	max. 260 °C
Time within 5 °C of actual peak temperature	between 10 and 30 seconds
Cool-down rate (Peak to 50 °C)	less than 6 °C / second
Time from 30 °C to Peak temperature	no greater than 300 seconds

Chip-mount air reflow profile

Vectron International GmbH
Potsdamer Straße 18
D 14 513 TELTOW / Germany
Tel: (+49) 3328 4784-0 / Fax: (+49) 3328 4784-30
E-Mail: tft@vectron.com

Vectron International GmbH reserves the right to make changes to the product(s) and/or information contained herein without notice. No liability is assumed as a result of their use or application. No rights under any patent accompany the sale of any such product(s) or information.

Vectron International**Filter specification****TFS1575Z****5/5****History**

Version	Reason of Changes	Name	Date
1.0	- Generation of development specification	Noack	09.07.2010
2.0	- Change of data table according to new customer requirements	Noack	23.07.2010
3.0	- Change alignment of tape and reel - Add typical values and filter characteristic - Generation of filter specification	Noack	27.05.2011
4.0	- updated data table - updated package drawing - updated stability characteristics - updated Tape & Reel	P. Jaster	07.06.2018
5.0	- updated filter characteristic - updated package	P. Jaster	11.06.2018

Vectron International GmbH
Potsdamer Straße 18
D 14 513 TELTOW / Germany
Tel: (+49) 3328 4784-0 / Fax: (+49) 3328 4784-30
E-Mail: tft@vectron.com

Vectron International GmbH reserves the right to make changes to the product(s) and/or information contained herein without notice. No liability is assumed as a result of their use or application. No rights under any patent accompany the sale of any such product(s) or information.