



## Part Number Search

You Searched For: CA3102E14S-6SA206 Go

Note: Data provided here are offered in good faith and are as reliable and accurate as possible. However, they do not form part of any contract of supply or purchase unless specifically confirmed in writing by an authorized representative of ITT. All information and images shown are the property of ITT ICS and are not to be reproduced in any form without direct authorization from ITT ICS.
*ITT ICS strongly recommends that you contact your local ITT Sales Office for confirmation of all the details you obtain through these Web pages. Please be aware that data may change at any time and without notice. For a listing of Sales Offices, local sales support, and authorized distributors please use the "Global Sales Locator" located either to the right of this data or at the top of every page.*



The requested part number is currently unsupported in our on-line configuration system. (d)

Product Datasheet

| | |
|---|---|
| Thread | Connector with threaded coupling |
| Shell Style | Box mounting receptacle |
| Gender | Socket |
| Shell Size | 14S |
| Contact Arrangement | 14S-6 |
| Number of contacts | 6 contacts size 16S |
| Contact Type | Solder Cup |
| Contact Plating | Hard silver |
| Shielding | no |
| Contact Rating at +20 °C (68 °F) (Size 15/15S/16/16S) | 22 A |
| Contact Resistance (Size 15/15S/16/16S) | 6 mΩ |
| Operating Voltage | In case of voltages greater than 50V the connector must be used in accordance with DIN VDE part 410, IEC 60364-4-41. |
| Insulator Resistance | Acc. To VG95319, part 2, test no. 5.12 and VG95210, part 32, test conditions B, standard insulator material > 1000 MΩ |
| Test Voltage | 1050 Vrms |
| Air and Creepage Paths (Min) | 0,7 mm |
| Ambient Temperature | Standard insulator material -55°/+125°C (-67/257°F) |
| Safety Provisions | IP67 acc. to DIN 40 050 (1 bar pressure after 12 hrs) |
| Salt Spray Resistance | 48 hours salt spray resistant |
| Mating Cycles | 500 min |
| Sep. Force per Contact (Size 15/15S/16/16S) | 1,0 N |
| Gage | For infos on Gage please see catalog VG95234, part 1 |
| Coupling Torque | Closing: 3,6 Nm max / Opening: 0,35 Nm min |
| Contact Retention (Size 15/15S/16/16S) | 35 N |
| Shell Material | Aluminium alloy |
| Shell Plating | Black Zinc Cobalt (conductive) |
| Insulator and Gromet Material | Neoprene |
| Contact Material | Copper alloy |
| Harnessing Info: Contact Cross-Section | See assembly instruction |
| Harnessing Info: Insulator Diameter | See assembly instruction |
| Wire Stripping (Size 15/15S/16/16S) | 6,2 mm |
| General Info | *All tests in accordance with VG95319 and/or if applicable with VG95210* |



© 2012 ITT Corporation. All rights reserved.

Downloaded from Arrow.com.