
SK1949

THIS DRAWING CONTAINS INFORMATION PROPRIETARY TO POSITRONIC AND IT'S SUBSIDIARIES. POSITRONIC BELIEVES THE DATA ON THIS DRAWING TO BE RELIABLE, SINCE THE TECHNICAL INFORMATION IS GIVEN FREE OF CHARGE, THE USER EMPLOYS SUCH INFORMATION AT HIS OWN DISCRETION AND RISK. POSITRONIC ASSUMES NO RESPONSIBILITY FOR RESULTS OBTAINED OR DAMAGES INCURRED FROM USE OF SUCH INFORMATION IN WHOLE OR IN PART.

DATE	REV	REVISION RECORD	APP	DR	CK
12-22-00	A	ECO 17176		YK	



NOTES:
1. MATERIALS AND FINISHES:
   INSULATOR: GLASS FILLED DAP PER ASTM-D-5948 TYPE SDG-F. GREY COLOR.
   SPACER, SLEEVES, AND KNOBS: ALUMINUM, YELLOW ANODIZE.
   JACKSCREWS: STAINLESS STEEL, PASSIVATED.
   WASHERS: STAINLESS STEEL, PASSIVATED.
   STRAIN RELIEF: STEEL, ZINC PLATE WITH DICHROMATE SEAL.
   SHELL: ALUMINUM, YELLOW ANODIZE.
2. ELECTRICAL CHARACTERISTICS:
   INSULATOR RESISTANCE: 5 G OHMS MINIMUM.
   WORKING TEMPERATURE: -65°C TO +150°C.
3. DIMENSIONS ARE IN INCHES [MILLIMETERS].

POSITRONIC INDUSTRIES INC.
www.connectpositronic.com
FSCM 28198

DECIMAL TOL. ±0.015 [0.38]
WF # 3297
ANGULAR TOL. ±5°

GMCT SERIES
SCALE N.T.S.
DRAWN BY Y. KELLEYBREW
APPROVED BY

TITLE
GMCT26M0E100J0

DATE 12-22-00
DRAWING NUMBER SK1949
REV. A

Downloaded from Arrow.com.