


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION –,– .
© COPYRIGHT – By – ALL RIGHTS RESERVED.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A1	ECR–18–010002	27JUN2018	GCM	AP





Terminal Dimensions
Customer to determine PCB pad dimensions.



Schematic

Electrical Specifications at +20°C unless noted otherwise

Test Description	Limit	Units	Tol	Notes
Inductance	51.00	µH	±5%	1–5, 100kHz, 100mVAC, Ls.
DC Resistance	0.41	Ω	Max	1–5
DC Resistance	0.18	Ω	Max.	10–9
DC Resistance	0.04	Ω	Max.	9–8
DC Resistance	0.19	Ω	Max.	6–7
Turns Ratio	2.64 : 1.00	––	±1%	(1–5) : (10–9), 100kHz, 100mVAC.
Turns Ratio	4.83 : 1.00	––	±1%	(1–5) : (9–8), 100kHz, 100mVAC.
Turns Ratio	3.22 : 1.00	––	±1%	(1–5) : (6–7), 100kHz, 100mVAC.
Dielectric	1500	VAC	500µA	1–10, 1 second test, 500µA maximum leakage current.
Dielectric	1500	VAC	500µA	1–6, 1 second test, 500µA maximum leakage current.
Dielectric	2500	VAC	500µA	6–core, 1 second test, 500µA maximum leakage current.

NOTES:

1. Operating Temperature Range: –40°C to +85°C
2. Terminal Plating is Hot–dipped SnAgCu over Ni
3. 265°C Maximum wave solder temperature per J–STD–020
4. All dimensions are in inches [millimeters].
5. As per MGPWT–00334 but with pins 2, 3 and 4 removed.

RoHS Compliant

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ± 0.5
1 PLC ± 0.2
2 PLC ± 0.1
3 PLC ± –
4 PLC ± –
ANGLES ± 5

MATERIAL –
FINISH –

DWN GANESH C M 11APR2018
CHK ALLAN P 11APR2018
APVD ALLAN P 11APR2018
PRODUCT SPEC —
APPLICATION SPEC —
WEIGHT

TE Connectivity Ltd.

NAME R1732–MGPWT–00334
–
–

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C–2176356	—

CUSTOMER DRAWING | SCALE NTS | SHEET 1 OF 1 | REV A1

Downloaded from Arrow.com.