

Part Number : 622018675

Product Description : Daughter Card Module Installation Press-In Tool for 3-Pair by 8-Column Assemblies

Series Number : 207123

Status : Obsolete

Product Category : Application Tooling Accessories

Engineering Number : 62201-8674



Documents & Resources

Tooling Specifications

[ATS-622018675-001.pdf](#)

[TM-622018799-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Product not active
China RoHS	Product not active
EU ELV	Product not active
Low-Halogen Status	Product not active
REACH SVHC	Product not active
EU RoHS	Product not active

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Obsolete
Category	Application Tooling Accessories
Series	207123
Description	Daughter Card Module Installation Press-In Tool for 3-Pair by 8- Column Assemblies
Comments	See Tooling Specification (PDF) Above
Function	Insertion
Geographic Area	Global
Level of Automation	Manual
More Detailed Tech Information	toolingsupport@molex.com
Product Name	Impact
Tool Type	Press-Fit Insertion Tool
UPC	883906297183
Warranty Disclaimer	<p>CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.</p>

Applicable Parts

Description	Part Number
Impact 85 Ohm Plus 3 Pair, RAM Signal Module, Right Guided, Open Endwalls, 8 Columns, 72 Circuits, Pin Length 4.90mm, Plated Through Hole Dimension 0.39mm, Lead Free	<u>1705109807</u>
Impact 100 Ohm 3 Pair Right-Angle Daughtercard Receptacle, Unguided, 8 Columns, 72 Circuits, Plated Through Hole Dimension 0.46mm, Lead-Free	<u>761701008</u>
Impact 100 Ohm 3 Pair Right-Angle Daughtercard Receptacle, Unguided, 8 Columns, 72 Circuits, Plated Through Hole Dimension 0.39mm, Lead-Free	<u>761701038</u>
Impact 100 Ohm 3 Pair Right-Angle Daughtercard Receptacle, Left Guided, 8 Columns, 72 Circuits, Plated Through Hole Dimension 0.46mm, Lead-Free	<u>761703008</u>
Impact 100 Ohm 3 Pair Right-Angle Daughtercard Receptacle, Left Guided, 8 Columns, 72 Circuits, Plated Through Hole Dimension 0.39mm, Lead-Free	<u>761703038</u>
Impact 100 Ohm 3 Pair Right-Angle Daughtercard Receptacle with ESD Clip, Left Guided, 8 Columns, 72 Circuits, Plated Through Hole Dimension 0.39mm, Lead-Free	<u>761703078</u>
Impact 100 Ohm 3 Pair Right-Angle Daughtercard Receptacle, Left Guided, 8 Columns, 72 Circuits, Plated Through Hole Dimension 0.39mm, Polarizing Key Position A, Lead-Free	<u>761703138</u>
Impact 100 Ohm 3 Pair Right-Angle Daughtercard Receptacle, Left	<u>761703538</u>

Guided, 8 Columns, 72 Circuits, Plated Through Hole Dimension 0.39mm, Polarizing Key Position E, Lead Free	
Impact 100 Ohm 3 Pair Right-Angle Daughtercard Receptacle, Right Guided, 8 Columns, 72 Circuits, Plated Through Hole Dimension 0.46mm, Lead-Free	<u>761705008</u>
Impact 100 Ohm 3 Pair Right-Angle Daughtercard Receptacle, Right Guided, 8 Columns, 72 Circuits, Plated Through Hole Dimension 0.39mm, Lead-Free	<u>761705038</u>
Impact 100 Ohm 3 Pair Right-Angle Daughtercard Receptacle, Right Guided, 8 Columns, 72 Circuits, Plated Through Hole Dimension 0.39mm, Polarizing Key Position B, Lead-Free	<u>761705138</u>
Impact 100 Ohm 3 Pair Right-Angle Male Header, Unguided, Open Endwall, 8 Columns, 72 Circuits, Pin Length 4.90mm, Plated Through Hole Dimension 0.46mm, Lead-Free	<u>764101804</u>
Impact 100 Ohm 3 Pair Right-Angle Male Header, Unguided, Open Endwall, 8 Columns, 72 Circuits, Pin Length 4.90mm, Plated Through Hole Dimension 0.39mm, Lead-Free	<u>764101807</u>
Impact 100 Ohm 3 Pair Right-Angle Male Header, Unguided, Open Endwall, 8 Columns, 72 Circuits, Pin Length 5.50mm, Plated Through Hole Dimension 0.39mm, Lead-Free	<u>764101808</u>
Impact 100 Ohm 3 Pair Right-Angle Male Header, Unguided, Dual Endwall, 8 Columns, 72 Circuits, Pin Length 4.90mm, Plated Through Hole Dimension 0.39mm,	<u>764101827</u>

Lead-Free	
Impact 100 Ohm 3 Pair Right-Angle Male Header, Left Guide, Open Endwall, 8 Columns, 72 Circuits, Pin Length 4.90mm, Plated Through Hole Dimension 0.46mm, Lead-Free	<u>764103804</u>
Impact 100 Ohm 3 Pair Right-Angle Male Header, Left Guide, Open Endwall, 8 Columns, 72 Circuits, Pin Length 4.90mm, Plated Through Hole Dimension 0.39mm, Lead-Free	<u>764103807</u>
Impact 100 Ohm 3 Pair Right-Angle Male Header, Left Guided, Open Endwall, 8 Columns, 72 Circuits, Pin Length 5.50mm, Plated Through Hole Dimension 0.39mm, Lead Free	<u>764103808</u>
Impact 100 Ohm 3 Pair Right-Angle Male Header, Left Guide, Open Endwall, 8 Columns, 72 Circuits, Pin Length 5.50mm, Plated Through Hole Dimension 0.39mm, Keying Orientation A, Lead-Free	<u>764103818</u>
Impact 100 Ohm 3 Pair Right-Angle Male Header, Right Guide, Open Endwall, 8 Columns, 72 Circuits, Pin Length 4.90mm, Plated Through Hole Dimension 0.46mm, Lead-Free	<u>764105804</u>
Impact 100 Ohm 3 Pair Right-Angle Male Header, Right Guide, Open Endwall, 8 Columns, 72 Circuits, Pin Length 4.90mm, Plated Through Hole Dimension 0.39mm, Lead-Free	<u>764105807</u>
Impact 100 Ohm 3 Pair Right-Angle Male Header, Right Guide, Open Endwall, 8 Columns, 72 Circuits, Pin Length 5.50mm, Plated Through Hole Dimension 0.39mm, Keying Orientation A, Lead-Free	<u>764105818</u>
Impact 100 Ohm 3 Pair Right-Angle Male Header, Left Guide, Right Endwall, 8 Columns, 72 Circuits, Pin	<u>764107807</u>

Length 4.90mm, Plated Through Hole Dimension 0.39mm, Lead-Free	
Impact 100 Ohm 3 Pair Right-Angle Male Header, Right Guided, Left Endwall, 8 Columns, 72 Circuits, Pin Length 4.90mm, Plated Through Hole Dimension 0.39mm, Lead Free	<u>764109807</u>
Impact 100 Ohm 3 Pair Right-Angle Male Header, Right Guided, Left Endwall, 8 Columns, 72 Circuits, Pin Length 5.50mm, Plated Through Hole Dimension 0.39mm, Lead Free	<u>764109808</u>
Impact 85 Ohm Plus 3 Pair Right-Angle Daughtercard, Unguided, 8 Columns, 72 Circuits, Plated Through Hole Dimension 0.39mm, Lead Free	<u>1705301038</u>
Impact 85 Ohm Plus 3 Pair Right-Angle Daughtercard, Left Guide, 8 Columns, 72 Circuits, Plated Through Hole Dimension 0.39mm, Lead Free	<u>1705303038</u>
Impact 85 Ohm Plus 3 Pair Right-Angle Daughtercard, Right Guide, 8 Columns, 72 Circuits, Plated Through Hole Dimension 0.39mm, Lead Free	<u>1705305038</u>

This document was generated on Sep 13, 2025