



APPROVED: _____
 DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	1/18/19	
A		UPDATE DRAWING	8/11/20	AY/DH

D




D



RECOMMENDED PCB LAYOUT

C

C



B

B

SPECIFICATIONS:**Material:**

Insulator: Nylon46, rated UL 94V-0

Insulator color: Black

Pin Header: Phosphor Bronze, Tin plated

Clips: Stainless steel

Electrical:

Voltage rating: 300 V

Current rating: 10 A

Dielectric withstanding voltage: 2,000 VAC for 1 minute

Mechanical:Wire range: 24~14AWG, 1.5mm²

Wire strip length: 8.0~9.0mm

Temperature Rating:

-40°C to +105°C

Environmental:

Lead free, RoHS compliant.

PACKAGED ON TAPE & REEL

Positions: 01 thru XX

A= .197 [5.00] x No. of Positions

B= .197 [5.00] x No. of Space

UNLESS OTHERWISE SPECIFIED
 ALL DIMENSIONS ARE INCHES [MM]
 TOLERANCES: EXCEPT AS NOTED
 INCHES HOLES
 .X ± .10 ØX ± .10
 .XX ± .020 ØXX ± .015
 .XXX ± .015 ØXXX ± .010

APPROVALS

DATE

DRAWN AY 1/18/19

CHECKED DH 1/18/19

APPROVED

ADAM
TECH
INTERCONNECTS 909 Rahway Avenue,
 Union, NJ 07083
 Phone: 908-687-5000
 Fax: 908-687-5710

TITLE .197 [5.00] PITCH SPRING CLAMP

TERMINAL BLOCKS, RIGHT ANGLE

SIZE X	PART NO. EB170-XX-C-BK-NY46-T/R	REV. A
REF: S00046C	SCALE: NTS	SHEET 1 OF 1

RoHS
 COMPLIANT