





REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A1	NEW DRAWING	23AUG2023	NK	JDB
	B1	DRAWING RE-CREATED IN CREO	22DEC2023	NK	JDB
	B2	REEL CORE DIA CHANGE	24 JUL2024	SS	LET




TAPE AND REEL PACKAGING ACCORDING TO
DIN IEC 60286-3
PACKAGING UNIT; 100 PCS



SCALE 2:1
3D VIEW



PCB-LAYOUT PROPOSAL



1	-	TAPE AND REEL	5
1	-	SOLDER CLIP LEFT	4
1	-	SOLDER CLIP RIGHT	3
3	-	PINS	2
1	-	M8 HOUSING	1
464431-E	REV	DESCRIPTION	ITEM NO.
-	REV OF EACH ASSY NO. (WHEN BLANK, USE DWG. REV)		
QTY	PARTS LIST		

V=TURNED CONTACT (PCB SIDE CAN BE USED WITH POTTED COMPOUND)

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN N K NIKHIL 22AUG2023 CHK M SZELAG 24AUG2023 APVD J DE BRUIJN 24AUG2023		 TE Connectivity	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: ISO 2768-mK ISO 8015		NAME M8 FEMALE, A CODE, 3P, 16.25MM SMT V	
		0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±		PRODUCT SPEC 108-94887 APPLICATION SPEC 114-94781	
MATERIAL - -		FINISH -		SIZE A 3 CAGE CODE 00779 DRAWING NO C-464431-E RESTRICTED TO -	
CUSTOMER DRAWING				SCALE	SHEET 1 OF 1 REV B2






NAME	M8 FEMALE, A CODE, 3P, 16.25MM SMT V
------	--------------------------------------

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
------	-----------	------------	---------------

A 3 00779 C-464431-E

CUSTOMER DRAWING	SCALE 5.1	SHEET 1 OF 1	REV B2
------------------	-----------	--------------	--------



INSPECTION LEVEL 1: CONTROL CHART REQUIRED
(1) PROOF OF PROCESS CAPABILITY OR 100% TEST IF PROCESS CAPABILITY IS NOT ACHIEVED

INSPECTION LEVEL 2 AND 3: CONTROL CHART REQUIRED
 (12) PROOF OF MEAN VALUE, STANDARD DEVIATION AND MACHINE CAPABILITY

(/3) PROOF OF VALUES OR PROOF OF ATTRIBUTIVE TEST

1. COPLANARITY OF ALL CONTACTS AND CLIPS $\leq 0.1\text{mm}$

