




Technical data

- 1.Nominal voltage: 300V/15A
PITCH:7.62mm
- 2.Insulation Withstanding Voltage:
AC 1600V/MIN
- 3.Insulation Resistance:
1000MΩ or more at DC500V
- 4.Operating temperature range:-40°C~115°C
- 5.Soldering temperature range:250°C±10°C/5sec
- 6.Safety approval:
- 7.RoHS Compliance
- 8.Undimensioned Tolerances:

Dim.L=(P-1)x7.62+18.2		
Dim.B=(P-1)x7.62		
P= number of poles 2-16P		
0-30mm	±0.15	±0.20
over 30mm-60mm	±0.20	±0.25
over 60mm-90mm	±0.25	±0.30
over 90mm	±0.30	±0.40

Part No.:

OSTOQXX0550

No. of Poles
02 2 Poles
03 3 Poles
... ..
16 16 Poles

COLOR
0: Black
2: Red
3: Orange
4: Yellow
5: Green (Standard)
6: Blue
8: Grey

Nonstandard colors
Mins could apply

3	FLANGE NUT	BRASS						2
2	PIN	COPPER				TIN PLATED		P
1	BODY	PA66 UL94V-0				ALL COLOR		1
ITEM	NAME OF PART		MATERIAL				NOTES	Q'TY
DWG.	Marvin Zhang	DATE	2019.01.15	UNITS:	MM	SHEET:	1 OF 1	Tolerance
CHK.	Marvin Zhang	DATE	2019.01.15	SCALE:	NONE 3:1 (:)	REV.: A		X. ±0.50
APP.		DATE		TITLE:	OSTOQ 7.62 Series W/F type Vertical (180D)		X.X ±0.30	±0.10
				PART NO.	OSTOQXX0550		X° ±1°	
				DWG NO.	OSTOQXX0550.dwg			
 ON-SHORE TECHNOLOGY, INC.								

REV	SIGN	DESCRIPTION	CHK.	DATE