2198230-3 ✔ ACTIVE



HSIO



TE Internal #: 2198230-3

SFP+, Cage Assembly, Signal, Operating Temperature Range -55 – 105 °C [-67 – 221 °F], Data Rate (Max) 16 Gb/s, 2 Ports

View on TE.com >

Connectors > High Speed Pluggable IO Connectors & Cages

Pluggable I/O Product Type: **Cage Assembly**

Sealable: **No**

Circuit Application: **Signal**

Operating Temperature Range: **-55 – 105 °C [-67 – 221 °F]**

Data Rate (Max): **16 Gb/s**

Features

Product Type Features

Cage Type	Ganged
Thermal Accessory Type Included	Heat Sink
Pluggable I/O Product Type	Cage Assembly
Sealable	No
Form Factor	SFP+

Configuration Features

Number of Ports	2
Port Matrix Configuration	1 x 2

Electrical Characteristics

Data Rate (Max)	16 Gb/s

Body Features

Heat Sink Style	Pin
Heat Sink Height	9.1 mm[.358 in]
Heat Sink Height Class	Networking Short

Downloaded from Arrow.com.

Termination Features

Termination Method to PCB	Through Hole - Press-Fit
Termination Post & Tail Length	2.05 mm[.081 in]

Housing Features

Cage Material	Nickel Silver

Dimensions

PCB Thickness (Recommended)	2.25 mm[.089 in]

Usage Conditions

Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]

Operation/Application

Pluggable I/O Applications	SFP+ Enhanced
Heat Sink Compatible	Yes
Circuit Application	Signal

Packaging Features

Packaging Method	Tray

Other

Included Lightpipe	No
EMI Containment Feature Type	Internal/External EMI Springs

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Downloaded from Arrow.com.

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

Compatible Parts



TE Part # 2127933-1
C/A, SFP+, GENERIC, 0.5M



TE Part # 2821224-8
SFP28 DIRECT ATTACH CA, 5M, 26AWG



TE Part # 2334985-2
SFP28 DIRECT ATTACH CA, 1M, 32AWG



TE Part # 2127933-7
C/A, SFP+, GENERIC, 6.0M



TE Part # 2127931-1
C/A, SFP+, GENERIC, 0.5M



TE Part # 2110759-1
PT CONN ASSY 20 POS 16G SFP



TE Part # 2334236-2
QSFP TO [4]SFP+, 28G, 30AWG, 1 METER



TE Part # 2334236-4
QSFP TO [4]SFP 25GIG 30AWG 2 METER



TE Part # 4-2821222-5
SFP56 DIRECT ATTACH CA, 2M, 30AWG



TE Part # 2127933-2
C/A, SFP+, GENERIC, 1.0M



TE Part # 2127933-5
C/A, SFP+, GENERIC, 4.0M



TE Part # 1-2334878-0
QSFP TO [4]SFP 25GIG 26AWG 5 METER

Downloaded from Arrow.com.



TE Part # 2334878-6
QSFP TO [4]SFP 25GIG 26AWG 3 METER



TE Part # 2127931-4
C/A, SFP+, GENERIC, 3.0M



TE Part # 2007182-1
SFP Standard 1x2 Light Pipe Assm



TE Part # 2821222-2
SFP28 DIRECT ATTACH CA, 2M, 30AWG



TE Part # 2821224-7
SFP28 DIRECT ATTACH CA, 4M, 26AWG



TE Part # 2127933-3
C/A, SFP+, GENERIC, 2.0M



TE Part # 2127931-3
C/A, SFP+, GENERIC, 2.0M




TE Part # 2127932-6
C/A, SFP+, GENERIC, 5.0M

Customers Also Bought




TE Part #5-147279-4
04 MODII HDR DR SFMT B/A T&R LF



TE Part #2-1761606-7
IDC LOW PRO HDR 20P VERT LA




TE Part #1977223-6
FSM2JSMAASTR=6MM TACT SWITCH,



TE Part #2170088-1
ZSFP+ Connector,30u"



TE Part #2170704-2
CAGE ASSY, QSFP28 1X1, SPRING, HS




TE Part #2227303-3
CAGE ASSEMBLY, SFP, .071 TAIL



TE Part #2325864-2
SFP-DD RECEPTACLE W HOLD DOWNS ASSEMBLY



TE Part #2332141-6
RECEPTACLE ASSY, 56POS, VERT, SLIVER 2.0



TE Part #5-2057691-1
IMP,R3PR8C,LG0.37E,Sn

TE Part #2274001-3
ZSFP+ 1X1 CAGE ASSEMBLY PRESSFIT

Documents

Downloaded from Arrow.com.

CAD Files

Customer View Model

ENG_CVM_CVM_2198230-3_A.2d_dxf.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2198230-3_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2198230-3_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the **Terms and Conditions** of use.

Product Specifications

Application Specification

English

Downloaded from Arrow.com.