

Representative Image

Catalog No. L-8-18-9-M

Description: CABLE TIE 18LB 8 NAT NYLON 1-PC BU

UPC No 728494917900

Home > Wire & Cable Management > Catamount > Cable ties

Cable Tie, Natural Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F) for Indoor Applications, Length of 203mm (7.99 Inches), Width of 2.5mm (0.10 Inches), Thickness of 1.2mm (0.05 Inches), Tensile Strength Rating of 80 Newtons (18 Pounds), Bulk Pack

Descriptors

Category	Cable ties

Specifications

Material	Nylon/Polyamide 6.6
Color	Natural
Lock Mechanism	Plastic Pawl
Tensile Strength	18 pounds , 80 newtons

Classifications

Brand Name	Catamount
Standard	UL E49405

Dimensions

Width	0.1 in , 2.54 mm
Length	7.99 in , 203 mm
Thickness	0.05 in , 1.2 mm
Bundle Diameter	0.0625 to 2 in , 1.59 to 50.8 mm

Compliance and Certifications

RoHS	RoHS3 Compliant
REACH	REACH 253 Compliant
TSCA	TSCA Section 6(h) Compliant

ETIM	EC000046 Cable tie
Band width	2.5 mm
Length belt/tape/tie	203 mm
Length belt/tape/tie	8 inch

by ABB

Downloaded from Arrow.com.

ETIM	EC000046 Cable tie
Tie thickness	1.2 mm
Tie thickness	0.05 inch
Min. holding force	80 N
Model	Internal toothing
Band closure	Plastic lip/-cam
Material	Plastic
Material quality	Polyamide (PA)
Surface protection	Untreated
Halogen free	Y
Colour	Natural colour
Transparent	N
Reflective (fluorescent)	N
Text strip	None
Solvable fastener	N
MIL approval	N

Certification/Standard

CLASS	File Number	Class	CCN	Certificate Number	Library Number
UL	E49405	N/A	N/A	N/A	N/A

Downloaded from Arrow.com.