

Sensors > Shock Sensors

How to check EU RoHS Compliance of Our Products is [here](#).

Product Lifecycle Stage	in Production
Recommended Rank	Non-Preferred
Replacement	This product is in production, but PKGS-25WXP1-R is strongly recommended in supply capacity.

Details

Global Part Number	PKGS-25NBP1-R
Previous Part Number	
Primary Axis Inclined Angle	25deg.
Sensitivity (Typ.)	0.168pC/G
Capacitance (Typ.)	520pF
Insulation Resistance (min.)	500M ohm
Resonant Frequency (Typ.)	44kHz
Non-linearity (Typ.)	1%
Transverse Sensitivity (Typ.)	2%
Shock Resistance	1500G (0.5ms duration)
Min Operating Temp. Range	-40...
Max Operating Temp. Range	85...
Min Storage Temp. Range	-40...
Max Storage Temp. Range	85...
Application	For consumer use
Sensitivity Type	Electric charge sensitivity type
Note	

-  [Part Numbering](#)
-  [Appearance](#)
-  [Dimensions](#)
-  [Primary axis inclined angle](#)
-  [Features and Applications](#)
-  [Freq. Characteristics](#)
-  [Reflow Chart](#)
-  [Notice\(other\)](#)
-  [Taping Dimensions](#)
-  [Reel Dimensions](#)
-  [Standard Land Patterns](#)

Minimum Quantity

180mm Paper Tape	
180mm Embossed Tape	3000
330mm Paper Tape	
330mm Embossed Tape	
Bulk Case	
Bulk(Bag)	
Ammo Pack	
320Reel	
Magazine	
Box	

Please make sure to read the Murata's [Product Policy](#), too.

All products and company names herein are trademarks or registered trademarks of their respective owners.