




Part Number : [878910408](#)
Product Description : KK 254 PCB Header,
Through Hole, Breakaway, Vertical, 4 Circuit,
2.50µm Tin (Sn) Overall Plating, Tray
Packaging, Lead-Free
Series Number : 87891
Status : Active
Product Category : PCB Headers and
Receptacles



Documents & Resources


Drawings
[878910408_sd.pdf](#)
[PK-89990-489-001.pdf](#)
[PK-89990-934-001.pdf](#)

3D Models and Design Files
[878910408_stp.zip](#)

Specifications
[PS-87920-019-001.pdf](#)
[879200000-TS-000.pdf](#)
[879200001-TS-000.pdf](#)

Product Environment Compliance

Compliance

| | |
|--------------------|---|
| GADSL/IMDS | Compliant with Exemption 44; 33 |
| China RoHS |  |
| EU ELV | Compliant per 2000/53/EC |
| Low-Halogen Status | Low-Halogen per IEC 61249-2-21 |
| REACH SVHC | Not Contained per D(2024)6225-DC (07 Nov 2024) |
| EU RoHS | Compliant per EU 2015/863 |

Multiple Part Product Compliance Statements
- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

| | |
|----------------|---|
| Status | Active |
| Category | PCB Headers and Receptacles |
| Series | 87891 |
| Description | KK 254 PCB Header, Through Hole, Breakaway, Vertical, 4 Circuit, 2.50µm Tin (Sn) Overall Plating, Tray Packaging, Lead-Free |
| Application | Board-to-Board, Signal, Wire-to-Board |
| Component Type | PCB Header |
| Product Name | KK 254 |
| UPC | 884982061507 |

Agency

| | |
|----|--------|
| UL | E29179 |
|----|--------|

Electrical

| | |
|-------------------------------|------|
| Current - Maximum per Contact | 3.0A |
| Voltage - Maximum | 250V |

Physical

| | |
|-------------------------|-------|
| Breakaway | Yes |
| Circuits (Loaded) | 4 |
| Circuits (maximum) | 4 |
| Color - Resin | Black |
| First Mate / Last Break | No |
| Flammability | 94V-0 |

| | |
|--------------------------------|----------------|
| Glow-Wire Capable | No |
| Guide to Mating Part | No |
| Keying to Mating Part | None |
| Lock to Mating Part | None |
| Mated Height | 25.54mm |
| Material - Metal | Copper Alloy |
| Material - Plating Mating | Tin |
| Material - Plating Termination | Nickel |
| Material - Resin | Nylon |
| Net Weight | 0.496/g |
| Number of Rows | 1 |
| Orientation | Vertical |
| Packaging Type | Tray |
| PC Tail Length | 2.97mm |
| PCB Locator | No |
| PCB Retention | None |
| PCB Thickness - Recommended | 1.60mm |
| Pitch - Mating Interface | 2.54mm |
| Pitch - Termination Interface | 2.54mm |
| Plating min - Mating | 2.540µm |
| Plating min - Termination | 1.270µm |
| Polarized to Mating Part | No |
| Polarized to PCB | No |
| Shrouded | No |
| Stackable | No |
| Temperature Range - Operating | -55° to +105°C |
| Termination Interface Style | Through Hole |

Mates With / Use With

Mates with Part(s)

| Description | Part Number |
|---------------------------|-------------|
| KK 254 PC Board Connector | <u>4455</u> |

| | |
|---|--------------|
| SL Single Row Female Insulation Displacement Connector Assemblies | <u>70400</u> |
| C-Grid III Vertical Single Row PC Board Connectors | <u>90147</u> |
| C-Grid III Right-Angle Single Row PC Board Connectors | <u>90148</u> |

This document was generated on Mar 03, 2025