

Series D xx P 24A 6 xx 12 LF

Number of contacts
09 , 15 , 25

Contacts
P : Pin

Termination

Code	Type	Foot Print/Pitch	Length of termination	PCB thickness
24A	Straight version	6 / 2.84mm	2	1.6

Plating
6 = 500 Mating / Unmating Mini

Packaging specification
Tape and Reel

See Note RoHS

NOTE RoHS iNFORMATION

- The "LF" product meet european union Directives and other country regulations asdescribed in GS-22-008.
- The housing will whistand exposure to 260° peak temperature for 30 seconds in a convection , infra-red or vapor reflow oven. See application notes/procedures if are available.
- Termination plating spec:1.27μ Nickel mini,2.5 to 7.5μ Sn(pure mate)
- Shell plating : Nickel bright
- Accessories : Sn pure bright
- Packaging spec ; See GS-14-920

Mounting Options

RL	Insert M3
RV	Female Screw UNC 4-40
RX	Insert UNC 4-40


Product Specification




see : GS-12-372

Packaging Specification


See GS-14-1054

litr	ecn no	dr	date
A	-	LH	03/02/06
B	LS06-0040	PC	23/03/06
C	LS06-0105	HLE	25/07/06
D	LS06-0220	PCR	2006/12/21
E	LS07-0050	HLE	2007/03/02
F	110-0120	NG	2010-05-27
G	110-0197	NG	2010-10-14

www.fciconnect.com			surface - 		tolerance std ISO 1302 ISO 406 ISO 1101		projection 		mm 			
			TOLERANCES UNLESS OTHERWISE SPECIFIED									
Dr	P.CRON	03/02/06	ANGULAR		LINEAR		0.X	±0.3	size A3	Scale 3:1		
Eng	H.LEGALLIC	03/02/06					0.XX	±0.1				
Chr	NIRMAL G	2010-10-14	0°	±2°			0.XXX	±0.05				
Appr	SUDHIR V	2010-10-14	Product family					SUB DELTA D PIP	Spec ref		-	
			title					SUB DELTA D PIP MALE			dwg no C01-8646-0876	Rev. G
			straight for tape and reel packaging									
			catalog no					SEE TABLE		CUSTOMER COPY		




Accessories details



TRUE POSITIONING : $\varnothing 0.36$

SHELL	P/N LEAD FREE	A ±0.38	B ±0.10	C ±0.10	D +0.25 0	E +0.15 0	F	G
09	D09P24A6xx12LF	30.81	24.99	16.96	16.79	5.9	10.96	8.22
15	D15P24A6xx12LF	39.14	33.32	25.18	25.12	5.9	19.18	16.44
25	D2524A6xx12LF	53.03	47.04	39.12	38.84	5.7	33.12	30.36

www.fciconnect.com			surface -  ISO 1302		tolerance std ISO 406 ISO 1101		projection 		mm 	
			TOLERANCES UNLESS OTHERWISE SPECIFIED							
Dr	P. CRON	03/02/06	ANGULAR	LINEAR	0.X	±0.3	size A2	Scale 3:1		
Eng	H. LEGALLIC	03/02/06			0.XX	±0.1				
Chr	NIRMAL G	2010-10-14			0°. ±2°	0.XXX			±0.05	
Appr	SUDHIR V	2010-10-14	Product family SUB DELTA D PIP				ECN 110-0197		Spec ref -	
			title SUB DELTA D PIP MALE				diag no C01-8646-0876		Rev. G	
			straight for tape and reel packaging							
			catalog no SEE TABLE				CUSTOMER COPY		sheet 2 of 2	